

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640576

Luminaire Tested: ML5612LSFL4097FS1E - 592SC - 600LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P640576  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-25)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSFL4097FS1E - 592SC - 600LM - 2700K  
Description: ML56 RR, 40D TIR OPTIC, 5" SPECULAR CLEAR TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 970.3 lumens  
Efficiency: N/A  
Efficacy: 94.2 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P640576  
CATALOG NUMBER: ML5612LSFL4097FS1E - 592SC - 600LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P640576

CATALOG NUMBER: ML5612LSFL4097FS1E - 592SC - 600LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	92	89	101	96	91	88	93	90	87		91	88	85		89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80		86	82	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		81	78	75		80	77	74	72
6	89	81	75	71	88	80	75	71	79	74	70		77	73	70		76	72	70	68
7	85	77	71	67	84	76	70	67	75	70	66		73	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	63	59		67	62	59		66	62	59	57
10	75	65	60	56	74	65	60	56	64	59	56		63	59	56		63	59	56	55

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	129566
5°	125274
10°	109264
15°	90119
20°	69617
25°	52252
30°	37619
35°	25663
40°	16045
45°	9121
50°	3242
55°	1872
60°	1074
65°	318
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9121 cd/sqm



TEST NUMBER: P640576

CATALOG NUMBER: ML5612LSFL4097FS1E - 592SC - 600LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.7	14.8
10°-20°	303.9	31.3
20°-30°	275.6	28.4
30°-40°	168.3	17.3
40°-50°	63.6	6.6
50°-60°	12.9	1.3
60°-70°	2.3	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	723.2	74.5
0°-40°	891.5	91.9
0°-60°	968.0	99.8
0°-90°	970.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	970.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1641	
5°	1581	144
15°	1103	304
25°	600	276
35°	266	168
45°	82	64
55°	14	13
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640576

CATALOG NUMBER: ML5612LSFL4097FS1E - 592SC - 600LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1641.3
2.5°	1628.6
5°	1580.9
7.5°	1486.5
10°	1363.1
12.5°	1234.6
15°	1102.7
17.5°	964.0
20°	828.7
22.5°	707.1
25°	599.9
27.5°	502.0
30°	412.7
32.5°	333.5
35°	266.3
37.5°	207.6
40°	155.7
42.5°	117.4
45°	81.7
47.5°	45.9
50°	26.4
52.5°	18.7
55°	13.6
57.5°	9.4
60°	6.8
62.5°	4.3
65°	1.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)