

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640651

Luminaire Tested: ML5612LSFL4097FS1E - 593WB - 600LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P640651  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSFL4097FS1E - 593WB - 600LM - 2700K  
Description: ML56 RR, 40D TIR OPTIC, 5" WHITE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 966.1 lumens  
Efficiency: N/A  
Efficacy: 93.8 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P640651

CATALOG NUMBER: ML5612LSFL4097FS1E - 593WB - 600LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P640651

CATALOG NUMBER: ML5612LSFL4097FS1E - 593WB - 600LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81			
4	98	90	85	81	96	89	84	80	87	83	79	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	85	76	70	66	83	75	69	66	74	69	65	72	68	65	71	67	64	63			
8	81	72	66	62	80	71	66	62	70	65	61	69	64	61	68	64	61	60			
9	77	68	62	58	76	67	62	58	66	62	58	66	61	58	65	61	58	56			
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	53			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	125342
5°	121312
10°	105874
15°	87021
20°	67802
25°	51704
30°	37446
35°	25576
40°	15952
45°	9489
50°	3758
55°	2464
60°	1752
65°	1121
70°	992
75°	1037
80°	1182
85°	1540

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9489 cd/sqm



TEST NUMBER: P640651

CATALOG NUMBER: ML5612LSFL4097FS1E - 593WB - 600LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.2	14.4
10°-20°	294.0	30.4
20°-30°	271.7	28.1
30°-40°	167.9	17.4
40°-50°	65.1	6.7
50°-60°	16.7	1.7
60°-70°	6.5	0.7
70°-80°	3.4	0.4
80°-90°	1.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	704.9	73.0
0°-40°	872.8	90.3
0°-60°	954.7	98.8
0°-90°	966.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	966.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1588	
5°	1531	139
15°	1065	294
25°	594	272
35°	265	168
45°	85	65
55°	18	17
65°	6	7
75°	3	3
85°	2	2
90°	0	



TEST NUMBER: P640651

CATALOG NUMBER: ML5612LSFL4097FS1E - 593WB - 600LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1587.8
2.5°	1577.6
5°	1530.9
7.5°	1439.9
10°	1320.8
12.5°	1191.5
15°	1064.8
17.5°	933.0
20°	807.1
22.5°	694.0
25°	593.6
27.5°	497.5
30°	410.8
32.5°	332.5
35°	265.4
37.5°	208.4
40°	154.8
42.5°	118.2
45°	85.0
47.5°	47.6
50°	30.6
52.5°	23.0
55°	17.9
57.5°	13.6
60°	11.1
62.5°	8.5
65°	6.0
67.5°	4.3
70°	4.3
72.5°	3.4
75°	3.4
77.5°	2.6
80°	2.6
82.5°	1.7
85°	1.7
87.5°	0.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)