

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640736

Luminaire Tested: ML5612LSFL4097FS1E - 692H - 1200LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P640736  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-38)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSFL4097FS1E - 692H - 1200LM - 2700K  
Description: ML56 RR, 40D TIR OPTIC, 6" HAZE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1508.3 lumens  
Efficiency: N/A  
Efficacy: 91.4 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 16.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P640736

CATALOG NUMBER: ML5612LSFL4097FS1E - 692H - 1200LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P640736

CATALOG NUMBER: ML5612LSFL4097FS1E - 692H - 1200LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	98	98	97	96	94			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82			
4	98	91	85	81	96	90	85	81	87	83	80	86	82	79	84	81	78	77			
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72			
6	89	80	75	70	87	80	74	70	78	73	70	77	72	69	75	72	69	67			
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63			
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60			
9	77	68	62	59	76	68	62	58	67	62	58	66	61	58	65	61	58	57			
10	74	65	59	55	73	64	59	55	64	59	55	63	58	55	62	58	55	54			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	136672
5°	132324
10°	115173
15°	94558
20°	73611
25°	55860
30°	40481
35°	27673
40°	17869
45°	10962
50°	5518
55°	2275
60°	1447
65°	519
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10962 cd/sqm



TEST NUMBER: P640736

CATALOG NUMBER: ML5612LSFL4097FS1E - 692H - 1200LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	218.4	14.5
10°-20°	460.1	30.5
20°-30°	423.6	28.1
30°-40°	262.4	17.4
40°-50°	113.4	7.5
50°-60°	25.6	1.7
60°-70°	4.8	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1102.1	73.1
0°-40°	1364.5	90.5
0°-60°	1503.5	99.7
0°-90°	1508.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1508.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2493	
5°	2405	218
15°	1666	460
25°	924	424
35°	414	262
45°	141	113
55°	24	26
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640736

CATALOG NUMBER: ML5612LSFL4097FS1E - 692H - 1200LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2493.1
2.5°	2476.0
5°	2404.6
7.5°	2258.0
10°	2069.0
12.5°	1869.5
15°	1666.1
17.5°	1457.3
20°	1261.8
22.5°	1083.4
25°	923.5
27.5°	775.6
30°	639.5
32.5°	519.2
35°	413.5
37.5°	323.7
40°	249.7
42.5°	192.9
45°	141.4
47.5°	104.4
50°	64.7
52.5°	34.4
55°	23.8
57.5°	18.5
60°	13.2
62.5°	7.9
65°	4.0
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)