

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641605

Luminaire Tested: ML5612LSVWFL97FS1E - 592H - 900LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641605
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-95)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 592H - 900LM - 5000K
Description: ML56 RR, MILKY OPTIC, 5" HAZE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1216.4 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.97
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641605
CATALOG NUMBER: ML5612LSVWFL97FS1E - 592H - 900LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P641605

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592H - 900LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77	77	77	77
4	95	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	71	71	71	71
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	64	61	60	60	60	60
7	79	69	62	58	78	68	62	57	67	61	57	66	61	57	64	60	56	55	55	55	55
8	75	64	58	53	73	64	57	53	63	57	53	61	56	53	60	56	52	51	51	51	51
9	71	60	54	49	70	60	53	49	59	53	49	58	53	49	57	52	49	47	47	47	47
10	67	56	50	46	66	56	50	46	55	50	46	54	49	46	54	49	45	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89622
5°	87706
10°	82547
15°	75752
20°	69214
25°	63114
30°	56661
35°	47944
40°	35037
45°	21881
50°	12490
55°	6826
60°	3521
65°	1625
70°	854
75°	366
80°	546
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21881 cd/sqm



TEST NUMBER: P641605

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592H - 900LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.2	8.5
10°-20°	259.7	21.4
20°-30°	332.3	27.3
30°-40°	304.7	25.1
40°-50°	156.7	12.9
50°-60°	47.7	3.9
60°-70°	9.9	0.8
70°-80°	1.9	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	695.2	57.2
0°-40°	999.9	82.2
0°-60°	1204.4	99.0
0°-90°	1216.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1216.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1135	
5°	1107	103
15°	927	260
25°	725	332
35°	498	305
45°	196	157
55°	50	48
65°	9	10
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P641605

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592H - 900LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1135.3
2.5°	1127.9
5°	1106.8
7.5°	1073.3
10°	1029.8
12.5°	979.0
15°	926.9
17.5°	874.7
20°	823.9
22.5°	774.2
25°	724.6
27.5°	673.7
30°	621.6
32.5°	563.3
35°	497.5
37.5°	420.6
40°	340.0
42.5°	263.0
45°	196.0
47.5°	142.7
50°	101.7
52.5°	70.7
55°	49.6
57.5°	33.5
60°	22.3
62.5°	13.6
65°	8.7
67.5°	5.0
70°	3.7
72.5°	2.5
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)