

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641645

Luminaire Tested: ML5612LSVWFL97FS1E - 593BB - 600LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641645
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-98)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 593BB - 600LM - 5000K
Description: ML56 RR, MILKY OPTIC, 5" BLACK BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 673.6 lumens
Efficiency: N/A
Efficacy: 65.4 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.11
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641645
CATALOG NUMBER: ML5612LSVWFL97FS1E - 593BB - 600LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P641645

CATALOG NUMBER: ML5612LSVWFL97FS1E - 593BB - 600LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58	58	58	58
7	78	67	60	56	76	67	60	56	65	59	55	64	59	55	63	58	55	53	53	53	53
8	73	63	56	51	72	62	55	51	61	55	51	60	54	51	59	54	50	49	49	49	49
9	69	58	52	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45	45	45	45
10	65	54	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26462
5°	26403
10°	26118
15°	25693
20°	25115
25°	24461
30°	23269
35°	20525
40°	15300
45°	9373
50°	5194
55°	2590
60°	1162
65°	376
70°	160
75°	212
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9373 cd/sqm



TEST NUMBER: P641645

CATALOG NUMBER: ML5612LSVWFL97FS1E - 593BB - 600LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.4	6.7
10°-20°	127.4	18.9
20°-30°	185.4	27.5
30°-40°	186.9	27.7
40°-50°	96.9	14.4
50°-60°	26.9	4.0
60°-70°	4.0	0.6
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	358.3	53.2
0°-40°	545.1	80.9
0°-60°	668.9	99.3
0°-90°	673.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	673.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	483	
5°	480	45
15°	453	127
25°	404	185
35°	307	187
45°	121	97
55°	27	27
65°	3	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P641645

CATALOG NUMBER: ML5612LSVWFL97FS1E - 593BB - 600LM - 5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	482.7
2.5°	481.8
5°	479.8
7.5°	475.0
10°	469.2
12.5°	461.4
15°	452.7
17.5°	442.1
20°	430.5
22.5°	417.9
25°	404.4
27.5°	387.9
30°	367.6
32.5°	341.5
35°	306.7
37.5°	263.1
40°	213.8
42.5°	163.5
45°	120.9
47.5°	87.1
50°	60.9
52.5°	41.6
55°	27.1
57.5°	17.4
60°	10.6
62.5°	5.8
65°	2.9
67.5°	1.9
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)