

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641822

Luminaire Tested: ML5612LSVWFL97FS1E - 693BB - 600LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641822  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-110)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL97FS1E - 693BB - 600LM - 3000K  
Description: ML56 RR, MILKY OPTIC, 6" BLACK BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 678.1 lumens  
Efficiency: N/A  
Efficacy: 65.8 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.21  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641822  
CATALOG NUMBER: ML5612LSVWFL97FS1E - 693BB - 600LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641822

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693BB - 600LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			
3	99	91	85	81	97	90	84	80	87	82	79	84	81	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	86	77	70	64	85	76	69	64	74	68	63	72	67	63	70	66	62	61			
6	81	70	63	58	79	70	63	58	68	62	57	66	61	57	65	60	57	55			
7	76	65	58	53	74	64	57	53	63	57	52	61	56	52	60	55	52	50			
8	71	60	53	48	70	59	53	48	58	52	48	57	52	48	56	51	47	46			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	43	42			
10	63	52	45	41	62	51	45	40	50	44	40	50	44	40	49	44	40	39			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	23112
5°	23052
10°	22929
15°	22685
20°	22396
25°	22005
30°	21370
35°	20371
40°	17841
45°	12614
50°	7309
55°	3766
60°	1721
65°	571
70°	144
75°	191
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12614 cd/sqm



TEST NUMBER: P641822

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693BB - 600LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.8	5.9
10°-20°	112.7	16.6
20°-30°	167.2	24.7
30°-40°	187.5	27.6
40°-50°	126.0	18.6
50°-60°	38.5	5.7
60°-70°	5.6	0.8
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	319.7	47.1
0°-40°	507.2	74.8
0°-60°	671.6	99.0
0°-90°	678.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	678.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	422	
5°	419	40
15°	400	113
25°	364	167
35°	304	187
45°	163	126
55°	39	38
65°	4	6
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P641822

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693BB - 600LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	421.6
2.5°	420.7
5°	418.9
7.5°	416.3
10°	411.9
12.5°	405.8
15°	399.7
17.5°	392.7
20°	383.9
22.5°	374.3
25°	363.8
27.5°	351.6
30°	337.6
32.5°	322.7
35°	304.4
37.5°	279.9
40°	249.3
42.5°	209.0
45°	162.7
47.5°	120.7
50°	85.7
52.5°	58.6
55°	39.4
57.5°	25.4
60°	15.7
62.5°	8.7
65°	4.4
67.5°	1.7
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)