

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641854

Luminaire Tested: ML5612LSVWFL97FS1E - 693TBZB - 600LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641854
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-112)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 693TBZB - 600LM - 4000K
Description: ML56 RR, MILKY OPTIC, 6" TUSCON BRONZE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 786.6 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.21
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641854
CATALOG NUMBER: ML5612LSVWFL97FS1E - 693TBZB - 600LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641854

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693TBZB - 600LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	69	76	72	69	67			
5	86	76	69	64	85	75	69	64	73	68	63	72	67	63	70	66	62	60			
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55			
7	76	65	58	53	74	64	57	52	63	57	52	61	56	52	60	55	52	50			
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46			
9	67	56	49	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42			
10	63	52	45	40	62	51	45	40	50	44	40	49	44	40	49	44	40	38			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26993
5°	26937
10°	26653
15°	26294
20°	25844
25°	25332
30°	24618
35°	23370
40°	20560
45°	14699
50°	8580
55°	4530
60°	2116
65°	882
70°	305
75°	212
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14699 cd/sqm



TEST NUMBER: P641854

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693TBZB - 600LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.4	5.9
10°-20°	130.6	16.6
20°-30°	192.6	24.5
30°-40°	215.6	27.4
40°-50°	146.2	18.6
50°-60°	46.4	5.9
60°-70°	7.8	1.0
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	369.6	47.0
0°-40°	585.2	74.4
0°-60°	777.8	98.9
0°-90°	786.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	786.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	492	
5°	490	46
15°	463	131
25°	419	193
35°	349	216
45°	190	146
55°	47	46
65°	7	8
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P641854

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693TBZB - 600LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	492.4
2.5°	491.4
5°	489.5
7.5°	484.6
10°	478.8
12.5°	472.0
15°	463.3
17.5°	454.6
20°	443.0
22.5°	431.4
25°	418.8
27.5°	404.3
30°	388.9
32.5°	371.4
35°	349.2
37.5°	322.1
40°	287.3
42.5°	240.9
45°	189.6
47.5°	141.2
50°	100.6
52.5°	70.6
55°	47.4
57.5°	31.9
60°	19.3
62.5°	11.6
65°	6.8
67.5°	2.9
70°	1.9
72.5°	1.0
75°	1.0
77.5°	1.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)