

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641940

Luminaire Tested: ML5612LSWFL5597FS1E - 592H - 1200LM - 5000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641940  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-49)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSWFL5597FS1E - 592H - 1200LM - 5000K  
Description: ML56 RR, 55D TIR OPTIC, 5" HAZE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1686.7 lumens  
Efficiency: N/A  
Efficacy: 102.2 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.88  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 16.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641940  
CATALOG NUMBER: ML5612LSWFL5597FS1E - 592H - 1200LM - 5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641940  
 CATALOG NUMBER: ML5612LSWFL5597FS1E - 592H - 1200LM - 5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86		
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80		
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74		
5	91	82	76	72	89	82	76	72	80	75	71	78	74	70	76	73	70	68		
6	86	77	71	66	85	76	70	66	75	70	66	73	69	65	72	68	65	63		
7	82	72	66	62	80	71	66	61	70	65	61	69	64	61	68	64	60	59		
8	78	68	61	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55		
9	74	64	58	53	73	63	57	53	62	57	53	61	56	53	60	56	53	51		
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	50	48		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	147833
5°	141487
10°	133849
15°	125776
20°	113132
25°	95176
30°	76997
35°	59816
40°	43209
45°	25677
50°	8670
55°	3936
60°	1184
65°	280
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25677 cd/sqm



TEST NUMBER: P641940

CATALOG NUMBER: ML5612LSWFL5597FS1E - 592H - 1200LM - 5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	166.8	9.9
10°-20°	428.0	25.4
20°-30°	499.4	29.6
30°-40°	386.5	22.9
40°-50°	175.3	10.4
50°-60°	28.5	1.7
60°-70°	2.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1094.1	64.9
0°-40°	1480.6	87.8
0°-60°	1684.4	99.9
0°-90°	1686.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1686.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1873	
5°	1786	167
15°	1539	428
25°	1093	499
35°	621	386
45°	230	175
55°	29	28
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P641940

CATALOG NUMBER: ML5612LSWFL5597FS1E - 592H - 1200LM - 5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1872.7
2.5°	1848.7
5°	1785.5
7.5°	1723.9
10°	1669.8
12.5°	1608.2
15°	1539.0
17.5°	1448.9
20°	1346.7
22.5°	1224.9
25°	1092.7
27.5°	961.9
30°	844.7
32.5°	728.9
35°	620.7
37.5°	512.5
40°	419.3
42.5°	327.6
45°	230.0
47.5°	123.2
50°	70.6
52.5°	45.1
55°	28.6
57.5°	16.5
60°	7.5
62.5°	3.0
65°	1.5
67.5°	1.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)