

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642116

Luminaire Tested: ML5612LSWFL5597FS1E - 692H - 1200LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642116  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-61)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSWFL5597FS1E - 692H - 1200LM - 2700K  
Description: ML56 RR, 55D TIR OPTIC, 6" HAZE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1488.5 lumens  
Efficiency: N/A  
Efficacy: 90.2 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 16.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642116  
CATALOG NUMBER: ML5612LSWFL5597FS1E - 692H - 1200LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P642116

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692H - 1200LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67			
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62			
7	81	71	65	61	80	71	65	60	69	64	60	68	63	60	67	63	59	58			
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	55	54			
9	73	63	57	52	72	62	56	52	61	56	52	60	56	52	60	55	52	50			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	87504
5°	83915
10°	79218
15°	74546
20°	67375
25°	57227
30°	46672
35°	36433
40°	26950
45°	17521
50°	7215
55°	2781
60°	1305
65°	337
70°	208
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 17521 cd/sqm



TEST NUMBER: P642116

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692H - 1200LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	142.3	9.6
10°-20°	365.6	24.6
20°-30°	432.5	29.1
30°-40°	340.6	22.9
40°-50°	171.5	11.5
50°-60°	31.6	2.1
60°-70°	3.9	0.3
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	940.5	63.2
0°-40°	1281.0	86.1
0°-60°	1484.1	99.7
0°-90°	1488.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1488.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1596	
5°	1525	142
15°	1314	366
25°	946	432
35°	544	341
45°	226	171
55°	29	32
65°	3	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P642116

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692H - 1200LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1596.2
2.5°	1577.7
5°	1524.9
7.5°	1470.7
10°	1423.1
12.5°	1371.6
15°	1313.5
17.5°	1239.5
20°	1154.9
22.5°	1055.8
25°	946.1
27.5°	839.1
30°	737.3
32.5°	639.6
35°	544.4
37.5°	455.9
40°	376.6
42.5°	298.6
45°	226.0
47.5°	146.7
50°	84.6
52.5°	46.2
55°	29.1
57.5°	19.8
60°	11.9
62.5°	5.3
65°	2.6
67.5°	1.3
70°	1.3
72.5°	1.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)