

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642180

Luminaire Tested: ML5612LSWFL5597FS1E - 693SNB - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642180
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-65)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 693SNB - 1200LM - 5000K
Description: ML56 RR, 55D TIR OPTIC, 6" SATIN NICKLE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1682.2 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642180
CATALOG NUMBER: ML5612LSWFL5597FS1E - 693SNB - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P642180

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693SNB - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93			93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			86
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	69	76	72	69	67			67
6	86	76	70	65	84	75	70	65	74	69	65	72	68	64	71	67	64	62			62
7	81	71	65	60	80	71	65	60	69	64	60	68	63	60	67	63	59	58			58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	55	54			54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	49	56	52	48	47			47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97887
5°	93792
10°	88937
15°	83854
20°	75846
25°	64637
30°	52806
35°	41338
40°	30657
45°	19925
50°	8588
55°	3164
60°	1480
65°	389
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19925 cd/sqm



TEST NUMBER: P642180

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693SNB - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.4	9.5
10°-20°	411.1	24.4
20°-30°	488.3	29.0
30°-40°	386.4	23.0
40°-50°	196.1	11.7
50°-60°	36.7	2.2
60°-70°	4.2	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1058.8	62.9
0°-40°	1445.2	85.9
0°-60°	1678.0	99.7
0°-90°	1682.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1682.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1786	
5°	1704	159
15°	1478	411
25°	1069	488
35°	618	386
45°	257	196
55°	33	37
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642180

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693SNB - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1785.6
2.5°	1764.5
5°	1704.4
7.5°	1648.8
10°	1597.7
12.5°	1540.6
15°	1477.5
17.5°	1394.8
20°	1300.1
22.5°	1188.9
25°	1068.6
27.5°	949.9
30°	834.2
32.5°	724.5
35°	617.7
37.5°	518.5
40°	428.4
42.5°	341.2
45°	257.0
47.5°	168.3
50°	100.7
52.5°	54.1
55°	33.1
57.5°	22.5
60°	13.5
62.5°	6.0
65°	3.0
67.5°	1.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)