

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642391

Luminaire Tested: ML5615LSFL409FS1E - 592SC - 1500LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-25)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 592SC - 1500LM - 2700K
Description: ML56 RR, 40D TIR OPTIC, 5" SPECULAR CLEAR TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1774.2 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642391
CATALOG NUMBER: ML5615LSFL409FS1E - 592SC - 1500LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P642391
 CATALOG NUMBER: ML5615LSFL409FS1E - 592SC - 1500LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94	
2	108	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88			88	
3	103	97	92	89	101	96	91	88	93	90	87	91	88	85	89	86	84	82			82	
4	98	91	86	82	97	90	85	81	88	84	80	86	82	80	84	81	79	77			77	
5	94	86	80	76	92	85	80	76	83	79	75	81	78	75	80	77	74	72			72	
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	70	68			68	
7	85	77	71	67	84	76	70	67	75	70	66	73	69	66	72	69	66	64			64	
8	82	72	67	63	80	72	67	63	71	66	63	70	65	62	69	65	62	61			61	
9	78	69	63	59	77	68	63	59	67	63	59	67	62	59	66	62	59	57			57	
10	75	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	55			55	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	236910
5°	229058
10°	199788
15°	164783
20°	127296
25°	95533
30°	68784
35°	46932
40°	29338
45°	16679
50°	5919
55°	3427
60°	1958
65°	579
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16679 cd/sqm



TEST NUMBER: P642391

CATALOG NUMBER: ML5615LSFL409FS1E - 592SC - 1500LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	262.8	14.8
10°-20°	555.6	31.3
20°-30°	503.8	28.4
30°-40°	307.8	17.3
40°-50°	116.4	6.6
50°-60°	23.6	1.3
60°-70°	4.2	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1322.3	74.5
0°-40°	1630.0	91.9
0°-60°	1770.0	99.8
0°-90°	1774.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1774.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3001	
5°	2891	263
15°	2016	556
25°	1097	504
35°	487	308
45°	149	116
55°	25	24
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642391

CATALOG NUMBER: ML5615LSFL409FS1E - 592SC - 1500LM - 2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3001.1
2.5°	2977.8
5°	2890.6
7.5°	2717.9
10°	2492.4
12.5°	2257.4
15°	2016.3
17.5°	1762.7
20°	1515.3
22.5°	1292.9
25°	1096.8
27.5°	917.9
30°	754.6
32.5°	609.9
35°	487.0
37.5°	379.6
40°	284.7
42.5°	214.7
45°	149.4
47.5°	84.0
50°	48.2
52.5°	34.2
55°	24.9
57.5°	17.1
60°	12.4
62.5°	7.8
65°	3.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)