

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642428

Luminaire Tested: ML5615LSFL409FS1E - 593BB - 900LM - 3500K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642428  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-29)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSFL409FS1E - 593BB - 900LM - 3500K  
Description: ML56 RR, 40D TIR OPTIC, 5" BLACK BAFFLE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1170.7 lumens  
Efficiency: N/A  
Efficacy: 111.5 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642428  
CATALOG NUMBER: ML5615LSFL409FS1E - 593BB - 900LM - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P642428

CATALOG NUMBER: ML5615LSFL409FS1E - 593BB - 900LM - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94		
2	108	104	100	97	106	102	99	96	99	96	93	96	94	92	93	91	90	88		
3	103	97	92	89	101	96	91	88	93	90	87	91	88	85	89	86	84	82		
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77		
5	94	86	80	76	92	85	80	76	83	79	75	81	78	74	80	77	74	72		
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68		
7	85	76	71	67	84	76	70	67	75	70	66	73	69	66	72	68	65	64		
8	81	72	67	63	80	72	66	63	71	66	62	70	65	62	69	65	62	61		
9	78	69	63	59	77	68	63	59	67	62	59	66	62	59	66	62	59	57		
10	75	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	54		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	155435
5°	150418
10°	131051
15°	107510
20°	83772
25°	63645
30°	46078
35°	31079
40°	19291
45°	11097
50°	3893
55°	2188
60°	1168
65°	392
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11097 cd/sqm



TEST NUMBER: P642428

CATALOG NUMBER: ML5615LSFL409FS1E - 593BB - 900LM - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.6	14.7
10°-20°	363.5	31.1
20°-30°	334.8	28.6
30°-40°	204.8	17.5
40°-50°	76.6	6.5
50°-60°	15.6	1.3
60°-70°	2.7	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	871.0	74.4
0°-40°	1075.8	91.9
0°-60°	1168.0	99.8
0°-90°	1170.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1170.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1969	
5°	1898	173
15°	1316	364
25°	731	335
35°	322	205
45°	99	77
55°	16	16
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642428

CATALOG NUMBER: ML5615LSFL409FS1E - 593BB - 900LM - 3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1969.0
2.5°	1955.3
5°	1898.2
7.5°	1787.1
10°	1634.9
12.5°	1476.2
15°	1315.5
17.5°	1152.7
20°	997.2
22.5°	855.5
25°	730.7
27.5°	613.3
30°	505.5
32.5°	407.1
35°	322.5
37.5°	252.7
40°	187.2
42.5°	141.7
45°	99.4
47.5°	53.9
50°	31.7
52.5°	23.3
55°	15.9
57.5°	11.6
60°	7.4
62.5°	5.3
65°	2.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)