

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642455

Luminaire Tested: ML5615LSFL409FS1E - 593TBZB - 1500LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642455
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-31)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 593TBZB - 1500LM - 5000K
Description: ML56 RR, 40D TIR OPTIC, 5" TUSCON BRONZE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1964.6 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642455
CATALOG NUMBER: ML5615LSFL409FS1E - 593TBZB - 1500LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P642455

CATALOG NUMBER: ML5615LSFL409FS1E - 593TBZB - 1500LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88				88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82				82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77				77
5	94	86	80	76	92	85	80	76	83	79	75	81	77	74	80	76	74	72				72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68				68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64				64
8	81	72	67	63	80	72	66	63	71	66	62	70	65	62	69	65	62	61				61
9	78	69	63	59	77	68	63	59	67	62	59	66	62	59	66	62	59	57				57
10	75	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	54				54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	260126
5°	251864
10°	219194
15°	180115
20°	140418
25°	106917
30°	77225
35°	52666
40°	32626
45°	18365
50°	6730
55°	3895
60°	2226
65°	654
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18365 cd/sqm



TEST NUMBER: P642455

CATALOG NUMBER: ML5615LSFL409FS1E - 593TBZB - 1500LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	288.7	14.7
10°-20°	609.1	31.0
20°-30°	561.6	28.6
30°-40°	345.5	17.6
40°-50°	128.2	6.5
50°-60°	26.8	1.4
60°-70°	4.7	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1459.3	74.3
0°-40°	1804.8	91.9
0°-60°	1959.9	99.8
0°-90°	1964.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1964.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3295	
5°	3178	289
15°	2204	609
25°	1228	562
35°	546	346
45°	164	128
55°	28	27
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642455

CATALOG NUMBER: ML5615LSFL409FS1E - 593TBZB - 1500LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3295.2
2.5°	3272.2
5°	3178.4
7.5°	2985.6
10°	2734.5
12.5°	2474.5
15°	2203.9
17.5°	1931.5
20°	1671.5
22.5°	1434.5
25°	1227.5
27.5°	1027.6
30°	847.2
32.5°	686.3
35°	546.5
37.5°	426.3
40°	316.6
42.5°	238.8
45°	164.5
47.5°	88.4
50°	54.8
52.5°	38.9
55°	28.3
57.5°	19.5
60°	14.1
62.5°	8.8
65°	3.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)