

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642556

Luminaire Tested: ML5615LSFL409FS1E - 692H - 1500LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642556  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-38)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSFL409FS1E - 692H - 1500LM - 2700K  
Description: ML56 RR, 40D TIR OPTIC, 6" HAZE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1775.7 lumens  
Efficiency: N/A  
Efficacy: 103.8 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 17.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642556  
CATALOG NUMBER: ML5615LSFL409FS1E - 692H - 1500LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P642556

CATALOG NUMBER: ML5615LSFL409FS1E - 692H - 1500LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	98	98	97	96	94			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82			
4	98	91	85	81	96	90	85	81	87	83	80	86	82	79	84	81	78	77			
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72			
6	89	80	75	70	87	80	74	70	78	73	70	77	72	69	75	72	69	67			
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63			
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60			
9	77	68	62	59	76	68	62	58	67	62	58	66	61	58	65	61	58	57			
10	74	65	59	55	73	64	59	55	64	59	55	63	58	55	62	58	55	54			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	160908
5°	155789
10°	135596
15°	111317
20°	86662
25°	65768
30°	47653
35°	32585
40°	21039
45°	12901
50°	6499
55°	2676
60°	1710
65°	610
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12901 cd/sqm



TEST NUMBER: P642556

CATALOG NUMBER: ML5615LSFL409FS1E - 692H - 1500LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	257.1	14.5
10°-20°	541.7	30.5
20°-30°	498.7	28.1
30°-40°	308.9	17.4
40°-50°	133.6	7.5
50°-60°	30.1	1.7
60°-70°	5.7	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1297.5	73.1
0°-40°	1606.4	90.5
0°-60°	1770.0	99.7
0°-90°	1775.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1775.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2935	
5°	2831	257
15°	1961	542
25°	1087	499
35°	487	309
45°	166	134
55°	28	30
65°	5	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642556

CATALOG NUMBER: ML5615LSFL409FS1E - 692H - 1500LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2935.2
2.5°	2915.0
5°	2831.0
7.5°	2658.3
10°	2435.9
12.5°	2201.0
15°	1961.4
17.5°	1715.7
20°	1485.5
22.5°	1275.5
25°	1087.3
27.5°	913.1
30°	752.8
32.5°	611.3
35°	486.9
37.5°	381.1
40°	294.0
42.5°	227.1
45°	166.4
47.5°	122.9
50°	76.2
52.5°	40.4
55°	28.0
57.5°	21.8
60°	15.6
62.5°	9.3
65°	4.7
67.5°	1.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)