

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642608

Luminaire Tested: ML5615LSFL409FS1E - 693BB - 900LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642608
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-41)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 693BB - 900LM - 3500K
Description: ML56 RR, 40D TIR OPTIC, 6" BLACK BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1189.7 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642608
CATALOG NUMBER: ML5615LSFL409FS1E - 693BB - 900LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P642608

CATALOG NUMBER: ML5615LSFL409FS1E - 693BB - 900LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82			
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77			
5	93	85	80	76	92	84	79	75	83	78	75	81	77	74	79	76	73	72			
6	89	80	75	70	88	80	74	70	78	73	70	77	73	69	75	72	69	67			
7	85	76	70	66	84	75	70	66	74	69	66	73	68	65	72	68	65	63			
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60			
9	77	68	62	59	76	68	62	59	67	62	58	66	61	58	65	61	58	57			
10	74	65	59	55	73	64	59	55	64	59	55	63	58	55	62	58	55	54			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107524
5°	104160
10°	90830
15°	74495
20°	58198
25°	44234
30°	32113
35°	21857
40°	14069
45°	8606
50°	4324
55°	1720
60°	1042
65°	415
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8606 cd/sqm



TEST NUMBER: P642608

CATALOG NUMBER: ML5615LSFL409FS1E - 693BB - 900LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.1	14.5
10°-20°	363.0	30.5
20°-30°	335.3	28.2
30°-40°	207.5	17.4
40°-50°	89.1	7.5
50°-60°	19.2	1.6
60°-70°	3.5	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	870.4	73.2
0°-40°	1077.9	90.6
0°-60°	1186.2	99.7
0°-90°	1189.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1189.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1961	
5°	1893	172
15°	1313	363
25°	731	335
35°	327	207
45°	111	89
55°	18	19
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642608

CATALOG NUMBER: ML5615LSFL409FS1E - 693BB - 900LM - 3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1961.4
2.5°	1950.9
5°	1892.8
7.5°	1780.7
10°	1631.7
12.5°	1472.1
15°	1312.6
17.5°	1151.9
20°	997.6
22.5°	857.1
25°	731.3
27.5°	614.0
30°	507.3
32.5°	411.1
35°	326.6
37.5°	255.7
40°	196.6
42.5°	152.2
45°	111.0
47.5°	81.4
50°	50.7
52.5°	26.4
55°	18.0
57.5°	12.7
60°	9.5
62.5°	6.3
65°	3.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)