

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642692

Luminaire Tested: ML5615LSFL409FS1E - 696WB - 1500LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642692
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-46)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 696WB - 1500LM - 3000K
Description: ML56 RR, 40D TIR OPTIC, 6" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1845.6 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642692
CATALOG NUMBER: ML5615LSFL409FS1E - 696WB - 1500LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P642692

CATALOG NUMBER: ML5615LSFL409FS1E - 696WB - 1500LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94	94	94	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87	87	87	87
3	103	96	91	87	101	95	90	87	92	89	85	90	87	84	88	85	83	81	81	81	81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76	76	76	76
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71	71	71	71
6	88	80	74	70	87	79	73	69	77	72	69	76	72	68	75	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63	63	63	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	67	62	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56	56	56	56
10	73	64	58	55	72	64	58	55	63	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	163962
5°	158958
10°	138730
15°	113769
20°	88686
25°	67105
30°	48368
35°	33167
40°	21734
45°	14125
50°	8315
55°	4588
60°	2631
65°	1453
70°	769
75°	339
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14125 cd/sqm



TEST NUMBER: P642692

CATALOG NUMBER: ML5615LSFL409FS1E - 696WB - 1500LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	262.7	14.2
10°-20°	553.3	30.0
20°-30°	508.6	27.6
30°-40°	315.0	17.1
40°-50°	144.1	7.8
50°-60°	46.7	2.5
60°-70°	12.2	0.7
70°-80°	2.5	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1324.5	71.8
0°-40°	1639.5	88.8
0°-60°	1830.3	99.2
0°-90°	1845.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1845.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2991	
5°	2889	263
15°	2005	553
25°	1109	509
35°	496	315
45°	182	144
55°	48	47
65°	11	12
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P642692

CATALOG NUMBER: ML5615LSFL409FS1E - 696WB - 1500LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2990.9
2.5°	2971.7
5°	2888.6
7.5°	2717.6
10°	2492.2
12.5°	2239.6
15°	2004.6
17.5°	1755.2
20°	1520.2
22.5°	1302.8
25°	1109.4
27.5°	928.8
30°	764.1
32.5°	620.2
35°	495.6
37.5°	391.6
40°	303.7
42.5°	236.6
45°	182.2
47.5°	135.9
50°	97.5
52.5°	68.7
55°	48.0
57.5°	33.6
60°	24.0
62.5°	17.6
65°	11.2
67.5°	6.4
70°	4.8
72.5°	3.2
75°	1.6
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)