

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642728

Luminaire Tested: ML5615LSNFL259FS1E - 592H - 900LM - 3500K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642728  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSNFL259FS1E - 592H - 900LM - 3500K  
Description: ML56 RR, 25D TIR OPTIC, 5" HAZE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1111.5 lumens  
Efficiency: N/A  
Efficacy: 105.9 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642728  
CATALOG NUMBER: ML5615LSNFL259FS1E - 592H - 900LM - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P642728

CATALOG NUMBER: ML5615LSNFL259FS1E - 592H - 900LM - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74			
6	91	82	77	73	89	82	77	73	80	76	72	79	75	72	78	74	71	70			
7	87	78	73	69	86	78	72	69	76	72	68	75	71	68	74	71	68	66			
8	83	75	69	65	82	74	69	65	73	68	65	72	68	65	71	67	64	63			
9	80	71	66	62	79	71	65	62	70	65	62	69	65	62	68	64	61	60			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	61	59	57			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	234068
5°	214509
10°	159748
15°	95268
20°	60426
25°	47723
30°	37601
35°	29460
40°	21908
45°	12280
50°	3119
55°	1596
60°	1168
65°	392
70°	254
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12280 cd/sqm



TEST NUMBER: P642728

CATALOG NUMBER: ML5615LSNFL259FS1E - 592H - 900LM - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	235.1	21.2
10°-20°	333.3	30.0
20°-30°	252.0	22.7
30°-40°	191.7	17.2
40°-50°	84.3	7.6
50°-60°	11.8	1.1
60°-70°	2.9	0.3
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	820.4	73.8
0°-40°	1012.1	91.1
0°-60°	1108.2	99.7
0°-90°	1111.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1111.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2965	
5°	2707	235
15°	1166	333
25°	548	252
35°	306	192
45°	110	84
55°	12	12
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642728

CATALOG NUMBER: ML5615LSNFL259FS1E - 592H - 900LM - 3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2965.1
2.5°	2906.9
5°	2707.0
7.5°	2384.3
10°	1992.9
12.5°	1560.3
15°	1165.7
17.5°	886.5
20°	719.3
22.5°	624.1
25°	547.9
27.5°	475.0
30°	412.5
32.5°	355.4
35°	305.7
37.5°	262.3
40°	212.6
42.5°	158.7
45°	110.0
47.5°	58.2
50°	25.4
52.5°	15.9
55°	11.6
57.5°	9.5
60°	7.4
62.5°	4.2
65°	2.1
67.5°	1.1
70°	1.1
72.5°	1.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)