

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643480

Luminaire Tested: ML5615LSVWFL9FS1E - 593SNB - 900LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643480
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-99)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 593SNB - 900LM - 5000K
Description: ML56 RR, MILKY OPTIC, 5" SATIN NICKLE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 953.7 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.14
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643480

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593SNB - 900LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P643480

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593SNB - 900LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	84	81	77	82	79	76	74			
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			
6	81	71	64	59	80	70	63	58	68	62	58	67	62	58	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51			
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	50	45	66	56	49	45	55	49	45	54	48	44	53	48	44	43			
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49456
5°	49289
10°	48945
15°	48504
20°	47859
25°	46843
30°	44984
35°	40321
40°	31399
45°	21066
50°	12981
55°	7831
60°	4673
65°	2764
70°	1569
75°	1373
80°	1046
85°	996

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21066 cd/sqm



TEST NUMBER: P643480

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593SNB - 900LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.0	6.2
10°-20°	167.3	17.5
20°-30°	246.9	25.9
30°-40°	256.3	26.9
40°-50°	148.8	15.6
50°-60°	54.1	5.7
60°-70°	15.7	1.6
70°-80°	4.8	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	473.2	49.6
0°-40°	729.5	76.5
0°-60°	932.3	97.8
0°-90°	953.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	953.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	626	
5°	622	59
15°	594	167
25°	538	247
35°	418	256
45°	189	149
55°	57	54
65°	15	16
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P643480

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593SNB - 900LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	626.5
2.5°	625.4
5°	622.0
7.5°	617.4
10°	610.6
12.5°	602.6
15°	593.5
17.5°	582.2
20°	569.7
22.5°	554.9
25°	537.8
27.5°	518.5
30°	493.5
32.5°	461.6
35°	418.4
37.5°	367.3
40°	304.7
42.5°	243.3
45°	188.7
47.5°	142.1
50°	105.7
52.5°	78.5
55°	56.9
57.5°	40.9
60°	29.6
62.5°	20.5
65°	14.8
67.5°	10.2
70°	6.8
72.5°	5.7
75°	4.5
77.5°	3.4
80°	2.3
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)