

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643814

Luminaire Tested: ML5615LSWFL559FS1E - 593SNB - 1200LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643814
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-53)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSWFL559FS1E - 593SNB - 1200LM - 4000K
Description: ML56 RR, 55D TIR OPTIC, 5" SATIN NICKLE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1590.2 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643814

CATALOG NUMBER: ML5615LSWFL559FS1E - 593SNB - 1200LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P643814

CATALOG NUMBER: ML5615LSWFL559FS1E - 593SNB - 1200LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93			93
2	107	102	98	94	105	101	97	93	97	94	91	94	92	89	91	89	88	86			86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79			79
4	96	88	82	78	94	87	82	77	85	80	76	83	79	76	81	77	75	73			73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68			68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	71	67	64	63			63
7	81	72	65	61	80	71	65	61	70	64	60	68	64	60	67	63	60	58			58
8	77	67	61	57	76	67	61	56	65	60	56	64	60	56	63	59	56	54			54
9	73	63	57	53	72	63	57	53	62	56	53	61	56	52	60	55	52	51			51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	134981
5°	129229
10°	122539
15°	115527
20°	104623
25°	89183
30°	72886
35°	56964
40°	41344
45°	25688
50°	8830
55°	4156
60°	1595
65°	542
70°	323
75°	427
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25688 cd/sqm



TEST NUMBER: P643814

CATALOG NUMBER: ML5615LSWFL559FS1E - 593SNB - 1200LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.6	9.6
10°-20°	393.7	24.8
20°-30°	467.6	29.4
30°-40°	368.8	23.2
40°-50°	172.7	10.9
50°-60°	30.0	1.9
60°-70°	3.9	0.2
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1013.9	63.8
0°-40°	1382.7	87.0
0°-60°	1585.4	99.7
0°-90°	1590.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1590.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1710	
5°	1631	153
15°	1414	394
25°	1024	468
35°	591	369
45°	230	173
55°	30	30
65°	3	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P643814

CATALOG NUMBER: ML5615LSWFL559FS1E - 593SNB - 1200LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1709.9
2.5°	1688.3
5°	1630.8
7.5°	1577.6
10°	1528.7
12.5°	1476.9
15°	1413.6
17.5°	1336.0
20°	1245.4
22.5°	1140.4
25°	1023.9
27.5°	907.4
30°	799.6
32.5°	694.6
35°	591.1
37.5°	493.3
40°	401.2
42.5°	314.9
45°	230.1
47.5°	129.4
50°	71.9
52.5°	46.0
55°	30.2
57.5°	18.7
60°	10.1
62.5°	5.8
65°	2.9
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)