

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742673

Luminaire Tested: LD4D10D010-EU4DR650210IC9030-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P742673
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D10D010-EU4DR650210IC9030-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 875.7 lumens
Efficiency: N/A
Efficacy: 74.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P742673

CATALOG NUMBER: LD4D10D010-EU4DR650210IC9030-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P742673

CATALOG NUMBER: LD4D10D010-EU4DR650210IC9030-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94205
5°	94279
10°	97599
15°	97754
20°	90007
25°	76686
30°	58716
35°	41469
40°	24490
45°	9936
50°	3604
55°	2000
60°	1158
65°	646
70°	671
75°	507
80°	566
85°	376

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9936 cd/sqm



TEST NUMBER: P742673

CATALOG NUMBER: LD4D10D010-EU4DR650210IC9030-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.0	9.5
10°-20°	239.5	27.3
20°-30°	287.3	32.8
30°-40°	193.1	22.1
40°-50°	57.8	6.6
50°-60°	10.2	1.2
60°-70°	2.9	0.3
70°-80°	1.4	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	609.8	69.6
0°-40°	802.9	91.7
0°-60°	870.9	99.5
0°-90°	875.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	875.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	862	
5°	860	83
15°	864	239
25°	636	287
35°	311	193
45°	64	58
55°	10	10
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P742673

CATALOG NUMBER: LD4D10D010-EU4DR650210IC9030-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	862.2
2.5°	865.8
5°	859.6
7.5°	872.6
10°	879.7
12.5°	878.0
15°	864.2
17.5°	830.7
20°	774.1
22.5°	707.4
25°	636.1
27.5°	555.6
30°	465.4
32.5°	383.5
35°	310.9
37.5°	239.3
40°	171.7
42.5°	112.1
45°	64.3
47.5°	34.0
50°	21.2
52.5°	14.7
55°	10.5
57.5°	7.6
60°	5.3
62.5°	3.4
65°	2.5
67.5°	2.2
70°	2.1
72.5°	1.6
75°	1.2
77.5°	1.1
80°	0.9
82.5°	0.6
85°	0.3
87.5°	0.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)