

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742456

Luminaire Tested: LD4D10D010-EU4DR500210IC9035-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P742456
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D10D010-EU4DR500210IC9035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1152.1 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P742456
CATALOG NUMBER: LD4D10D010-EU4DR500210IC9035-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P742456
 CATALOG NUMBER: LD4D10D010-EU4DR500210IC9035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95			95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85			85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80			80
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76			76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72			72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69			69
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65			65
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62			62
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	202810
5°	200678
10°	197373
15°	179729
20°	149550
25°	106162
30°	56193
35°	22902
40°	8501
45°	3894
50°	1598
55°	838
60°	415
65°	129
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3894 cd/sqm



TEST NUMBER: P742456

CATALOG NUMBER: LD4D10D010-EU4DR500210IC9035-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.9	15.0
10°-20°	437.1	37.9
20°-30°	392.6	34.1
30°-40°	122.9	10.7
40°-50°	21.5	1.9
50°-60°	4.3	0.4
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1002.6	87.0
0°-40°	1125.6	97.7
0°-60°	1151.4	99.9
0°-90°	1152.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1152.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1856	
5°	1830	173
15°	1589	437
25°	881	393
35°	172	123
45°	25	22
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P742456

CATALOG NUMBER: LD4D10D010-EU4DR500210IC9035-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1856.2
2.5°	1847.0
5°	1829.7
7.5°	1803.5
10°	1779.0
12.5°	1700.8
15°	1588.9
17.5°	1446.8
20°	1286.2
22.5°	1100.5
25°	880.6
27.5°	647.4
30°	445.4
32.5°	290.0
35°	171.7
37.5°	98.6
40°	59.6
42.5°	38.8
45°	25.2
47.5°	15.4
50°	9.4
52.5°	6.4
55°	4.4
57.5°	3.0
60°	1.9
62.5°	1.1
65°	0.5
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)