

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742685

Luminaire Tested: LD4D10D010-EU4DR650210IC9035-4LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P742685  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D10D010-EU4DR650210IC9035-4LBDP1B  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 688.7 lumens  
Efficiency: N/A  
Efficacy: 58.9 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P742685

CATALOG NUMBER: LD4D10D010-EU4DR650210IC9035-4LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P742685

CATALOG NUMBER: LD4D10D010-EU4DR650210IC9035-4LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	74079
5°	74142
10°	76753
15°	76873
20°	70775
25°	60302
30°	46163
35°	32612
40°	19255
45°	7819
50°	2839
55°	1581
60°	896
65°	491
70°	543
75°	422
80°	440
85°	376

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7819 cd/sqm



TEST NUMBER: P742685

CATALOG NUMBER: LD4D10D010-EU4DR650210IC9035-4LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.3	9.5
10°-20°	188.3	27.3
20°-30°	225.9	32.8
30°-40°	151.8	22.0
40°-50°	45.5	6.6
50°-60°	8.0	1.2
60°-70°	2.3	0.3
70°-80°	1.2	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	479.5	69.6
0°-40°	631.4	91.7
0°-60°	684.9	99.4
0°-90°	688.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	688.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	678	
5°	676	65
15°	680	188
25°	500	226
35°	244	152
45°	51	45
55°	8	8
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P742685

CATALOG NUMBER: LD4D10D010-EU4DR650210IC9035-4LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	678.0
2.5°	680.9
5°	676.0
7.5°	686.2
10°	691.8
12.5°	690.4
15°	679.6
17.5°	653.2
20°	608.7
22.5°	556.3
25°	500.2
27.5°	436.9
30°	365.9
32.5°	301.5
35°	244.5
37.5°	188.2
40°	135.0
42.5°	88.2
45°	50.6
47.5°	26.8
50°	16.7
52.5°	11.6
55°	8.3
57.5°	6.0
60°	4.1
62.5°	2.7
65°	1.9
67.5°	1.7
70°	1.7
72.5°	1.3
75°	1.0
77.5°	0.9
80°	0.7
82.5°	0.5
85°	0.3
87.5°	0.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)