

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742790

Luminaire Tested: LD4D10D010-EU4DR700210IC9050-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P742790
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D10D010-EU4DR700210IC9050-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1081.5 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P742790
CATALOG NUMBER: LD4D10D010-EU4DR700210IC9050-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P742790

CATALOG NUMBER: LD4D10D010-EU4DR700210IC9050-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			53
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			50
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132850
5°	128905
10°	125314
15°	123657
20°	115482
25°	86752
30°	61328
35°	21728
40°	11425
45°	12161
50°	12595
55°	12839
60°	12915
65°	12642
70°	11948
75°	11060
80°	9816
85°	8023

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 12915 cd/sqm



TEST NUMBER: P742790

CATALOG NUMBER: LD4D10D010-EU4DR700210IC9050-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.9	10.3
10°-20°	304.1	28.1
20°-30°	334.9	31.0
30°-40°	127.9	11.8
40°-50°	60.4	5.6
50°-60°	60.1	5.6
60°-70°	48.1	4.4
70°-80°	27.7	2.6
80°-90°	7.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	749.8	69.3
0°-40°	877.8	81.2
0°-60°	998.2	92.3
0°-90°	1081.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1081.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1216	
5°	1175	111
15°	1093	304
25°	720	335
35°	163	128
45°	79	60
55°	67	60
65°	49	48
75°	26	28
85°	6	8
90°	0	



TEST NUMBER: P742790

CATALOG NUMBER: LD4D10D010-EU4DR700210IC9050-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1215.9
2.5°	1203.2
5°	1175.3
7.5°	1152.0
10°	1129.5
12.5°	1110.4
15°	1093.2
17.5°	1051.9
20°	993.2
22.5°	866.5
25°	719.6
27.5°	626.4
30°	486.1
32.5°	314.0
35°	162.9
37.5°	87.9
40°	80.1
42.5°	79.5
45°	78.7
47.5°	77.0
50°	74.1
52.5°	70.8
55°	67.4
57.5°	63.5
60°	59.1
62.5°	54.1
65°	48.9
67.5°	43.1
70°	37.4
72.5°	31.6
75°	26.2
77.5°	20.6
80°	15.6
82.5°	11.0
85°	6.4
87.5°	2.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)