

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743062

Luminaire Tested: LD4D15D010-EU4DR250215IC9030-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P743062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR250215IC9030-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1326.2 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743062
CATALOG NUMBER: LD4D15D010-EU4DR250215IC9030-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P743062

CATALOG NUMBER: LD4D15D010-EU4DR250215IC9030-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94	92	90	89
4	103	97	93	90	102	96	93	90	94	91	89		93	90	88		91	89	87	85
5	100	93	89	86	98	93	89	86	91	87	85		89	86	84		88	85	83	82
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85	83	80	79
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83	80	78	77
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80	77	75	74
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78	75	73	72
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76	73	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	549560
5°	511857
10°	365113
15°	215043
20°	133807
25°	73431
30°	33585
35°	12711
40°	5762
45°	3461
50°	1445
55°	933
60°	656
65°	440
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3461 cd/sqm



TEST NUMBER: P743062

CATALOG NUMBER: LD4D15D010-EU4DR250215IC9030-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	401.1	30.2
10°-20°	543.2	41.0
20°-30°	287.5	21.7
30°-40°	71.0	5.4
40°-50°	17.3	1.3
50°-60°	4.6	0.3
60°-70°	1.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1231.8	92.9
0°-40°	1302.7	98.2
0°-60°	1324.6	99.9
0°-90°	1326.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1326.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5030	
5°	4667	401
15°	1901	543
25°	609	287
35°	95	71
45°	22	17
55°	5	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P743062

CATALOG NUMBER: LD4D15D010-EU4DR250215IC9030-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5029.8
2.5°	4947.1
5°	4666.9
7.5°	4103.6
10°	3290.9
12.5°	2487.8
15°	1901.1
17.5°	1481.6
20°	1150.8
22.5°	863.0
25°	609.1
27.5°	408.5
30°	266.2
32.5°	162.0
35°	95.3
37.5°	58.3
40°	40.4
42.5°	30.9
45°	22.4
47.5°	13.5
50°	8.5
52.5°	6.1
55°	4.9
57.5°	3.8
60°	3.0
62.5°	2.3
65°	1.7
67.5°	0.6
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)