

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743138

Luminaire Tested: LD4D15D010-EU4DR300215IC9030-4LBS1LI

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P743138  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D15D010-EU4DR300215IC9030-4LBS1LI  
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1449.4 lumens  
Efficiency: N/A  
Efficacy: 91.7 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P743138  
CATALOG NUMBER: LD4D15D010-EU4DR300215IC9030-4LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P743138

CATALOG NUMBER: LD4D15D010-EU4DR300215IC9030-4LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	356730	356730	356730
5°	346491	346084	346506
10°	300109	297995	300039
15°	195811	194757	193782
20°	97364	101021	97234
25°	49044	55310	48039
30°	19639	21398	17111
35°	9111	8718	7317
40°	3937	4367	3707
45°	2771	3442	2793
50°	953	2501	1012
55°	547	1041	587
60°	383	459	383
65°	254	254	254
70°	157	112	157
75°	0	59	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 3442 cd/sqm



TEST NUMBER: P743138

CATALOG NUMBER: LD4D15D010-EU4DR300215IC9030-4LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	409.8	28.3
10°-20°	660.0	45.5
20°-30°	285.2	19.7
30°-40°	65.0	4.5
40°-50°	22.3	1.5
50°-60°	5.5	0.4
60°-70°	1.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1355.0	93.5
0°-40°	1420.0	98.0
0°-60°	1447.8	99.9
0°-90°	1449.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1449.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4660	4660	4660	4660	4660	
5°	4510	4505	4504	4514	4510	410
15°	2471	2441	2458	2450	2445	662
25°	581	603	655	587	569	278
35°	98	100	93	93	78	66
45°	26	32	32	32	26	18
55°	4	4	8	5	4	4
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P743138

CATALOG NUMBER: LD4D15D010-EU4DR300215IC9030-4LBS1LI

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4660.5	4660.5	4660.5	4660.5	4660.5
2.5°	4629.6	4626.4	4628.2	4630.5	4631.4
5°	4509.5	4505.1	4504.2	4513.6	4509.7
7.5°	4267.2	4261.0	4251.6	4272.8	4292.8
10°	3861.2	3854.4	3834.0	3844.0	3860.3
12.5°	3262.0	3239.8	3239.3	3271.3	3267.0
15°	2471.0	2441.2	2457.7	2449.7	2445.4
17.5°	1661.6	1650.2	1672.2	1665.5	1636.9
20°	1195.3	1198.3	1240.2	1219.1	1193.7
22.5°	872.3	883.0	932.6	878.4	858.5
25°	580.7	602.7	654.9	587.4	568.8
27.5°	357.2	367.3	420.1	352.6	342.5
30°	222.2	217.1	242.1	207.8	193.6
32.5°	145.8	139.3	147.4	132.2	120.8
35°	97.5	99.5	93.3	92.6	78.3
37.5°	60.8	70.0	61.8	65.9	50.4
40°	39.4	50.8	43.7	48.3	37.1
42.5°	32.3	39.1	35.9	38.2	32.9
45°	25.6	31.8	31.8	31.8	25.8
47.5°	14.2	21.3	27.2	21.7	15.1
50°	8.0	10.8	21.0	11.2	8.5
52.5°	5.5	6.2	14.4	6.4	5.7
55°	4.1	4.4	7.8	4.6	4.4
57.5°	3.2	3.4	4.1	3.4	3.2
60°	2.5	2.5	3.0	2.8	2.5
62.5°	1.8	1.8	2.1	1.8	1.8
65°	1.4	1.4	1.4	1.4	1.4
67.5°	0.7	0.9	0.9	0.9	0.9
70°	0.7	0.5	0.5	0.5	0.7
72.5°	0.5	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)