

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743736

Luminaire Tested: LD4D15D010-EU4DR700215IC9030-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P743736
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR700215IC9030-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 788.7 lumens
Efficiency: N/A
Efficacy: 49.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743736

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9030-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P743736

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9030-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96882
5°	94005
10°	91386
15°	90187
20°	84216
25°	63268
30°	44725
35°	15846
40°	8330
45°	8869
50°	9179
55°	9372
60°	9418
65°	9204
70°	8689
75°	8063
80°	7110
85°	5767

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 9436 cd/sqm



TEST NUMBER: P743736

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9030-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.8	10.3
10°-20°	221.8	28.1
20°-30°	244.2	31.0
30°-40°	93.3	11.8
40°-50°	44.0	5.6
50°-60°	43.8	5.6
60°-70°	35.1	4.4
70°-80°	20.1	2.6
80°-90°	5.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	546.8	69.3
0°-40°	640.1	81.2
0°-60°	728.0	92.3
0°-90°	788.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	788.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	887	
5°	857	81
15°	797	222
25°	525	244
35°	119	93
45°	57	44
55°	49	44
65°	36	35
75°	19	20
85°	5	5
90°	0	



TEST NUMBER: P743736

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9030-4LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	886.7
2.5°	877.4
5°	857.1
7.5°	840.1
10°	823.7
12.5°	809.8
15°	797.3
17.5°	767.1
20°	724.3
22.5°	631.9
25°	524.8
27.5°	456.8
30°	354.5
32.5°	229.0
35°	118.8
37.5°	64.2
40°	58.4
42.5°	58.0
45°	57.4
47.5°	56.1
50°	54.0
52.5°	51.7
55°	49.2
57.5°	46.4
60°	43.1
62.5°	39.5
65°	35.6
67.5°	31.5
70°	27.2
72.5°	23.0
75°	19.1
77.5°	15.0
80°	11.3
82.5°	8.0
85°	4.6
87.5°	1.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)