

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743377

Luminaire Tested: LD4D15D010-EU4DR450215IC9035-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P743377
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR450215IC9035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1528.3 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743377
CATALOG NUMBER: LD4D15D010-EU4DR450215IC9035-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P743377

CATALOG NUMBER: LD4D15D010-EU4DR450215IC9035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		98	98	97	95
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91	89	87	85
4	100	94	89	85	99	93	88	85	91	87	84		89	86	83		87	84	82	81
5	96	89	84	80	95	88	83	80	86	82	79		85	81	79		83	80	78	77
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80	77	74	73
7	89	81	75	72	87	80	75	72	79	74	71		78	74	71		77	73	71	69
8	85	77	72	68	84	76	71	68	75	71	68		74	70	67		73	70	67	66
9	82	73	68	65	81	73	68	65	72	68	65		71	67	64		71	67	64	63
10	79	70	65	62	78	70	65	62	69	65	62		68	64	61		68	64	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	295157
5°	286753
10°	274348
15°	251081
20°	199199
25°	124353
30°	68545
35°	30771
40°	12124
45°	5717
50°	2703
55°	1410
60°	699
65°	155
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5717 cd/sqm



TEST NUMBER: P743377

CATALOG NUMBER: LD4D15D010-EU4DR450215IC9035-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.7	16.1
10°-20°	604.6	39.6
20°-30°	478.8	31.3
30°-40°	159.4	10.4
40°-50°	31.7	2.1
50°-60°	7.2	0.5
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1329.0	87.0
0°-40°	1488.5	97.4
0°-60°	1527.3	99.9
0°-90°	1528.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1528.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2701	
5°	2614	246
15°	2220	605
25°	1032	479
35°	231	159
45°	37	32
55°	7	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P743377

CATALOG NUMBER: LD4D15D010-EU4DR450215IC9035-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2701.4
2.5°	2683.8
5°	2614.5
7.5°	2557.4
10°	2472.8
12.5°	2360.2
15°	2219.7
17.5°	2008.5
20°	1713.2
22.5°	1361.3
25°	1031.5
27.5°	755.4
30°	543.3
32.5°	369.5
35°	230.7
37.5°	136.8
40°	85.0
42.5°	55.9
45°	37.0
47.5°	23.8
50°	15.9
52.5°	10.6
55°	7.4
57.5°	4.9
60°	3.2
62.5°	1.7
65°	0.6
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)