

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743163

Luminaire Tested: LD4D15D010-EU4DR300215IC9040-4LBS1MW

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P743163  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D15D010-EU4DR300215IC9040-4LBS1MW  
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1423.5 lumens  
Efficiency: N/A  
Efficacy: 90.1 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P743163  
CATALOG NUMBER: LD4D15D010-EU4DR300215IC9040-4LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P743163

CATALOG NUMBER: LD4D15D010-EU4DR300215IC9040-4LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	350347	350347	350347
5°	340290	339891	340306
10°	294746	292663	294676
15°	192300	191270	190311
20°	95621	99213	95499
25°	48165	54314	47186
30°	19286	21018	16802
35°	8942	8569	7176
40°	3867	4287	3637
45°	2728	3377	2750
50°	929	2465	988
55°	547	1014	574
60°	383	444	383
65°	254	254	254
70°	157	112	157
75°	0	59	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 3377 cd/sqm



TEST NUMBER: P743163

CATALOG NUMBER: LD4D15D010-EU4DR300215IC9040-4LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	402.5	28.3
10°-20°	648.2	45.5
20°-30°	280.1	19.7
30°-40°	63.8	4.5
40°-50°	21.9	1.5
50°-60°	5.4	0.4
60°-70°	1.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1330.8	93.5
0°-40°	1394.6	98.0
0°-60°	1421.9	99.9
0°-90°	1423.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1423.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4577	4577	4577	4577	4577	
5°	4429	4425	4424	4433	4429	403
15°	2427	2398	2414	2406	2402	650
25°	570	592	643	577	559	273
35°	96	98	92	91	77	65
45°	25	31	31	31	25	18
55°	4	4	8	4	4	4
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P743163

CATALOG NUMBER: LD4D15D010-EU4DR300215IC9040-4LBS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4577.1	4577.1	4577.1	4577.1	4577.1
2.5°	4546.8	4543.6	4545.4	4547.7	4548.6
5°	4428.8	4424.6	4423.6	4432.9	4429.0
7.5°	4190.8	4184.8	4175.6	4196.5	4216.0
10°	3792.2	3785.4	3765.4	3775.3	3791.3
12.5°	3203.6	3181.8	3181.4	3212.8	3208.6
15°	2426.7	2397.6	2413.7	2405.9	2401.6
17.5°	1631.9	1620.7	1642.2	1635.7	1607.6
20°	1173.9	1176.8	1218.0	1197.3	1172.4
22.5°	856.6	867.2	916.0	862.7	843.2
25°	570.3	591.9	643.1	576.8	558.7
27.5°	350.8	360.7	412.6	346.3	336.4
30°	218.2	213.3	237.8	204.0	190.1
32.5°	143.1	136.9	144.7	129.9	118.7
35°	95.7	97.7	91.7	91.0	76.8
37.5°	59.8	68.8	60.7	64.7	49.4
40°	38.7	49.9	42.9	47.4	36.4
42.5°	31.7	38.4	35.3	37.5	32.4
45°	25.2	31.2	31.2	31.2	25.4
47.5°	13.9	20.9	26.8	21.4	14.8
50°	7.8	10.5	20.7	11.0	8.3
52.5°	5.4	6.1	14.2	6.3	5.6
55°	4.1	4.3	7.6	4.5	4.3
57.5°	3.2	3.4	4.1	3.4	3.2
60°	2.5	2.5	2.9	2.7	2.5
62.5°	1.8	1.8	2.0	1.8	1.8
65°	1.4	1.4	1.4	1.4	1.4
67.5°	0.7	0.9	0.9	0.9	0.9
70°	0.7	0.5	0.5	0.5	0.7
72.5°	0.5	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)