

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743094

Luminaire Tested: LD4D15D010-EU4DR250215IC9050-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P743094
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR250215IC9050-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1286.4 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743094

CATALOG NUMBER: LD4D15D010-EU4DR250215IC9050-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P743094

CATALOG NUMBER: LD4D15D010-EU4DR250215IC9050-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89			
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85			
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79			
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	533061
5°	496480
10°	354152
15°	208584
20°	129784
25°	71224
30°	32575
35°	12338
40°	5591
45°	3353
50°	1394
55°	895
60°	634
65°	440
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3353 cd/sqm



TEST NUMBER: P743094

CATALOG NUMBER: LD4D15D010-EU4DR250215IC9050-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	389.0	30.2
10°-20°	526.9	41.0
20°-30°	278.8	21.7
30°-40°	68.8	5.4
40°-50°	16.8	1.3
50°-60°	4.4	0.3
60°-70°	1.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1194.8	92.9
0°-40°	1263.6	98.2
0°-60°	1284.9	99.9
0°-90°	1286.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1286.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4879	
5°	4527	389
15°	1844	527
25°	591	279
35°	92	69
45°	22	17
55°	5	4
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P743094

CATALOG NUMBER: LD4D15D010-EU4DR250215IC9050-4LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	4878.8
2.5°	4798.6
5°	4526.7
7.5°	3980.4
10°	3192.1
12.5°	2413.0
15°	1844.0
17.5°	1437.1
20°	1116.2
22.5°	837.1
25°	590.8
27.5°	396.2
30°	258.2
32.5°	157.1
35°	92.5
37.5°	56.6
40°	39.2
42.5°	30.0
45°	21.7
47.5°	13.1
50°	8.2
52.5°	6.0
55°	4.7
57.5°	3.7
60°	2.9
62.5°	2.2
65°	1.7
67.5°	0.6
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)