

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743703

Luminaire Tested: LD4D15D010-EU4DR650215IC9050-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P743703
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR650215IC9050-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1394.2 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743703
CATALOG NUMBER: LD4D15D010-EU4DR650215IC9050-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P743703

CATALOG NUMBER: LD4D15D010-EU4DR650215IC9050-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73933
5°	73753
10°	73686
15°	71414
20°	65017
25°	56657
30°	47126
35°	37339
40°	26951
45°	17023
50°	8877
55°	4714
60°	2476
65°	1368
70°	564
75°	632
80°	437
85°	402

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17023 cd/sqm



TEST NUMBER: P743703

CATALOG NUMBER: LD4D15D010-EU4DR650215IC9050-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.7	8.6
10°-20°	327.8	23.5
20°-30°	400.7	28.7
30°-40°	325.1	23.3
40°-50°	162.0	11.6
50°-60°	45.2	3.2
60°-70°	10.3	0.7
70°-80°	2.7	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	848.3	60.8
0°-40°	1173.4	84.2
0°-60°	1380.6	99.0
0°-90°	1394.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1394.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1266	
5°	1258	120
15°	1181	328
25°	879	401
35°	524	325
45°	206	162
55°	46	45
65°	10	10
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P743703

CATALOG NUMBER: LD4D15D010-EU4DR650215IC9050-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1265.9
2.5°	1265.0
5°	1258.0
7.5°	1253.8
10°	1242.5
12.5°	1219.5
15°	1181.1
17.5°	1121.2
20°	1046.1
22.5°	965.0
25°	879.2
27.5°	787.5
30°	698.8
32.5°	611.1
35°	523.7
37.5°	436.4
40°	353.5
42.5°	275.7
45°	206.1
47.5°	143.6
50°	97.7
52.5°	67.3
55°	46.3
57.5°	31.2
60°	21.2
62.5°	14.7
65°	9.9
67.5°	5.0
70°	3.3
72.5°	3.2
75°	2.8
77.5°	1.8
80°	1.3
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)