

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739737

Luminaire Tested: LD4D02D010-EU4DR700210IC9040-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P739737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D02D010-EU4DR700210IC9040-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 298.1 lumens
Efficiency: N/A
Efficacy: 58.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P739737

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9040-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P739737

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9040-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36624
5°	35525
10°	34538
15°	34093
20°	31836
25°	23918
30°	16906
35°	5989
40°	3152
45°	3353
50°	3485
55°	3543
60°	3562
65°	3490
70°	3290
75°	3039
80°	2706
85°	2257

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 3562 cd/sqm



TEST NUMBER: P739737

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9040-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.6	10.2
10°-20°	83.8	28.1
20°-30°	92.3	31.0
30°-40°	35.3	11.8
40°-50°	16.7	5.6
50°-60°	16.6	5.6
60°-70°	13.3	4.4
70°-80°	7.6	2.6
80°-90°	2.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	206.7	69.3
0°-40°	242.0	81.2
0°-60°	275.2	92.3
0°-90°	298.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	298.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	335	
5°	324	31
15°	301	84
25°	198	92
35°	45	35
45°	22	17
55°	19	17
65°	14	13
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P739737

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9040-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	335.2
2.5°	331.6
5°	323.9
7.5°	317.5
10°	311.3
12.5°	306.1
15°	301.4
17.5°	289.9
20°	273.8
22.5°	238.9
25°	198.4
27.5°	172.7
30°	134.0
32.5°	86.6
35°	44.9
37.5°	24.2
40°	22.1
42.5°	21.9
45°	21.7
47.5°	21.2
50°	20.5
52.5°	19.5
55°	18.6
57.5°	17.5
60°	16.3
62.5°	14.9
65°	13.5
67.5°	11.9
70°	10.3
72.5°	8.7
75°	7.2
77.5°	5.7
80°	4.3
82.5°	3.0
85°	1.8
87.5°	0.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)