

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739740

Luminaire Tested: LD4D02D010-EU4DR700210IC9040-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P739740
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D02D010-EU4DR700210IC9040-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 421.9 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P739740
CATALOG NUMBER: LD4D02D010-EU4DR700210IC9040-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P739740

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9040-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78		
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71		
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65		
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56		
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48		
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36373
5°	36282
10°	36213
15°	36197
20°	35835
25°	33671
30°	30014
35°	23929
40°	15889
45°	9503
50°	4929
55°	2591
60°	918
65°	26
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9503 cd/sqm



TEST NUMBER: P739740

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9040-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.5	7.5
10°-20°	90.2	21.4
20°-30°	127.3	30.2
30°-40°	109.9	26.1
40°-50°	49.2	11.7
50°-60°	12.9	3.1
60°-70°	0.8	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	249.0	59.0
0°-40°	358.9	85.1
0°-60°	421.0	99.8
0°-90°	421.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	421.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	333	
5°	331	31
15°	320	90
25°	279	127
35°	179	110
45°	62	49
55°	14	13
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P739740

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9040-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	332.9
2.5°	332.6
5°	330.8
7.5°	329.4
10°	326.4
12.5°	323.6
15°	320.0
17.5°	315.9
20°	308.2
22.5°	295.8
25°	279.3
27.5°	260.2
30°	237.9
32.5°	210.7
35°	179.4
37.5°	145.0
40°	111.4
42.5°	84.7
45°	61.5
47.5°	42.4
50°	29.0
52.5°	20.0
55°	13.6
57.5°	8.2
60°	4.2
62.5°	1.3
65°	0.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)