

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745712

Luminaire Tested: LD4D25D010-EU4DR7020359040-4LBS1B

Issue Date: 1/31/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P745712  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/31/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D25D010-EU4DR7020359040-4LBS1B  
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2556.6 lumens  
Efficiency: N/A  
Efficacy: 101.9 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P745712  
CATALOG NUMBER: LD4D25D010-EU4DR7020359040-4LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P745712

CATALOG NUMBER: LD4D25D010-EU4DR7020359040-4LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78			
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71			
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65			
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60			
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56			
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51			
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48			
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	220477
5°	219927
10°	219452
15°	219398
20°	217244
25°	204077
30°	181940
35°	145054
40°	96318
45°	57573
50°	29848
55°	15696
60°	5550
65°	78
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 57573 cd/sqm



TEST NUMBER: P745712

CATALOG NUMBER: LD4D25D010-EU4DR7020359040-4LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	190.7	7.5
10°-20°	546.9	21.4
20°-30°	771.5	30.2
30°-40°	666.0	26.1
40°-50°	298.2	11.7
50°-60°	78.1	3.1
60°-70°	5.1	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1509.2	59.0
0°-40°	2175.2	85.1
0°-60°	2551.5	99.8
0°-90°	2556.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2556.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2018	
5°	2005	191
15°	1940	547
25°	1693	772
35°	1088	666
45°	373	298
55°	82	78
65°	0	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P745712

CATALOG NUMBER: LD4D25D010-EU4DR7020359040-4LBS1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2017.9
2.5°	2015.8
5°	2005.2
7.5°	1996.5
10°	1978.0
12.5°	1961.3
15°	1939.6
17.5°	1914.5
20°	1868.4
22.5°	1792.6
25°	1692.8
27.5°	1577.0
30°	1442.1
32.5°	1276.9
35°	1087.5
37.5°	878.5
40°	675.3
42.5°	513.1
45°	372.6
47.5°	256.9
50°	175.6
52.5°	121.2
55°	82.4
57.5°	49.7
60°	25.4
62.5°	8.0
65°	0.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)