

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745753

Luminaire Tested: LD4D30D010-EU4DR1515309027-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P745753
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR1515309027-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2895.2 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745753
CATALOG NUMBER: LD4D30D010-EU4DR1515309027-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P745753

CATALOG NUMBER: LD4D30D010-EU4DR1515309027-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4438642	4438642	4438642
5°	2608357	2574575	2594942
10°	778475	783924	795923
15°	193639	197408	191320
20°	57939	67087	59166
25°	20426	26019	20683
30°	7503	9877	7630
35°	3762	4241	3638
40°	2372	2606	2372
45°	1750	1869	1750
50°	1391	1391	1391
55°	1162	1162	1162
60°	941	941	941
65°	714	714	714
70°	607	607	607
75°	378	378	506
80°	260	260	260
85°	141	141	141

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 1869 cd/sqm



TEST NUMBER: P745753

CATALOG NUMBER: LD4D30D010-EU4DR1515309027-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1877.8	64.9
10°-20°	772.4	26.7
20°-30°	153.4	5.3
30°-40°	38.3	1.3
40°-50°	20.1	0.7
50°-60°	14.9	0.5
60°-70°	10.5	0.4
70°-80°	6.0	0.2
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2803.6	96.8
0°-40°	2841.9	98.2
0°-60°	2876.9	99.4
0°-90°	2895.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2895.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	39448	39448	39448	39448	39448	
5°	25666	25402	25333	25508	25534	1874
15°	2229	2271	2273	2233	2203	764
25°	262	297	334	296	266	138
35°	52	55	58	55	50	35
45°	25	25	27	25	25	20
55°	17	17	17	17	17	15
65°	10	10	10	10	10	11
75°	5	5	5	5	7	6
85°	2	2	2	2	2	2
90°	0	0	0	0	0	



TEST NUMBER: P745753

CATALOG NUMBER: LD4D30D010-EU4DR1515309027-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	39447.6	39447.6	39447.6	39447.6	39447.6
2.5°	35583.3	35613.4	35625.0	35660.1	35790.4
5°	25665.5	25401.6	25333.1	25508.5	25533.5
7.5°	15203.2	15256.7	15452.0	15495.5	15338.5
10°	8343.1	8411.5	8401.5	8461.6	8530.1
12.5°	4266.7	4213.3	4196.6	4265.1	4169.9
15°	2229.4	2271.1	2272.8	2232.7	2202.7
17.5°	1199.0	1247.5	1327.6	1262.5	1162.3
20°	708.1	751.5	819.9	766.5	723.1
22.5°	437.5	472.6	521.0	479.3	444.2
25°	262.2	297.3	334.0	295.6	265.5
27.5°	155.3	185.4	208.7	183.7	153.6
30°	100.2	116.9	131.9	115.2	101.9
32.5°	70.1	76.8	83.5	76.8	70.1
35°	51.8	55.1	58.4	55.1	50.1
37.5°	40.1	43.4	45.1	41.7	38.4
40°	33.4	35.1	36.7	35.1	33.4
42.5°	28.4	30.1	30.1	30.1	28.4
45°	25.0	25.0	26.7	25.0	25.0
47.5°	21.7	21.7	23.4	21.7	21.7
50°	20.0	20.0	20.0	20.0	20.0
52.5°	18.4	18.4	18.4	18.4	18.4
55°	16.7	16.7	16.7	16.7	16.7
57.5°	15.0	15.0	15.0	15.0	15.0
60°	13.4	13.4	13.4	13.4	13.4
62.5°	11.7	11.7	11.7	11.7	11.7
65°	10.0	10.0	10.0	10.0	10.0
67.5°	10.0	10.0	10.0	10.0	10.0
70°	8.3	8.3	8.3	8.3	8.3
72.5°	6.7	6.7	6.7	6.7	6.7
75°	5.0	5.0	5.0	5.0	6.7
77.5°	5.0	5.0	5.0	5.0	5.0
80°	3.3	3.3	3.3	3.3	3.3
82.5°	3.3	3.3	3.3	3.3	3.3
85°	1.7	1.7	1.7	1.7	1.7
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)