

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746193

Luminaire Tested: LD4D30D010-EU4DR4020359050-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P746193
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR4020359050-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2963.0 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P746193
CATALOG NUMBER: LD4D30D010-EU4DR4020359050-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P746193

CATALOG NUMBER: LD4D30D010-EU4DR4020359050-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96			96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92			92
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88			88
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84			84
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81			81
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77			77
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74			74
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72			72
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69			69
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67			67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	753757
5°	750089
10°	709002
15°	602745
20°	410815
25°	171406
30°	53897
35°	25049
40°	13849
45°	6351
50°	3094
55°	1695
60°	874
65°	310
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6351 cd/sqm



TEST NUMBER: P746193

CATALOG NUMBER: LD4D30D010-EU4DR4020359050-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	638.6	21.6
10°-20°	1430.6	48.3
20°-30°	716.1	24.2
30°-40°	131.3	4.4
40°-50°	36.2	1.2
50°-60°	8.5	0.3
60°-70°	1.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2785.3	94.0
0°-40°	2916.6	98.4
0°-60°	2961.3	99.9
0°-90°	2963.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2963.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6899	
5°	6839	639
15°	5329	1431
25°	1422	716
35°	188	131
45°	41	36
55°	9	9
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P746193

CATALOG NUMBER: LD4D30D010-EU4DR4020359050-4LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	6898.7
2.5°	6888.6
5°	6839.0
7.5°	6681.1
10°	6390.5
12.5°	5937.5
15°	5328.6
17.5°	4536.7
20°	3533.2
22.5°	2408.8
25°	1421.8
27.5°	751.6
30°	427.2
32.5°	276.0
35°	187.8
37.5°	134.2
40°	97.1
42.5°	66.5
45°	41.1
47.5°	26.2
50°	18.2
52.5°	12.9
55°	8.9
57.5°	5.6
60°	4.0
62.5°	2.4
65°	1.2
67.5°	0.8
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)