

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746776

Luminaire Tested: LD4D35BD010-EU4DR3020359030-4LBDP1LI

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P746776  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D35BD010-EU4DR3020359030-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3276.7 lumens  
Efficiency: N/A  
Efficacy: 106.4 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P746776

CATALOG NUMBER: LD4D35BD010-EU4DR3020359030-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P746776

CATALOG NUMBER: LD4D35BD010-EU4DR3020359030-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	806469	806469	806469
5°	783318	782403	783356
10°	678470	673690	678315
15°	442670	440293	438082
20°	220118	228378	219825
25°	110883	125038	108611
30°	44396	48373	38677
35°	20595	19726	16530
40°	8893	9872	8373
45°	6268	7783	6333
50°	2155	5668	2274
55°	1241	2349	1308
60°	873	1026	873
65°	561	561	561
70°	358	224	358
75°	0	148	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 7783 cd/sqm



TEST NUMBER: P746776

CATALOG NUMBER: LD4D35BD010-EU4DR3020359030-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	926.5	28.3
10°-20°	1492.1	45.5
20°-30°	644.8	19.7
30°-40°	147.0	4.5
40°-50°	50.5	1.5
50°-60°	12.3	0.4
60°-70°	3.2	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3063.4	93.5
0°-40°	3210.4	98.0
0°-60°	3273.1	99.9
0°-90°	3276.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3276.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	10536	10536	10536	10536	10536	
5°	10195	10185	10183	10204	10195	927
15°	5586	5519	5556	5538	5528	1496
25°	1313	1362	1480	1328	1286	628
35°	220	225	211	210	177	149
45°	58	72	72	72	58	41
55°	9	10	18	10	10	9
65°	3	3	3	3	3	3
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P746776

CATALOG NUMBER: LD4D35BD010-EU4DR3020359030-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	10536.1	10536.1	10536.1	10536.1	10536.1
2.5°	10466.3	10459.0	10463.2	10468.3	10470.4
5°	10194.7	10184.9	10182.8	10204.0	10195.2
7.5°	9646.9	9632.9	9611.7	9659.8	9704.8
10°	8729.2	8713.7	8667.7	8690.4	8727.2
12.5°	7374.5	7324.3	7323.2	7395.7	7385.8
15°	5586.2	5518.9	5556.2	5538.1	5528.3
17.5°	3756.5	3730.7	3780.3	3765.3	3700.7
20°	2702.3	2709.0	2803.7	2756.1	2698.7
22.5°	1971.9	1996.2	2108.5	1985.9	1940.9
25°	1312.9	1362.5	1480.5	1327.9	1286.0
27.5°	807.5	830.2	949.7	797.1	774.4
30°	502.3	490.9	547.3	469.7	437.6
32.5°	329.5	315.0	333.1	299.0	273.1
35°	220.4	225.0	211.1	209.5	176.9
37.5°	137.6	158.3	139.7	149.0	113.8
40°	89.0	114.8	98.8	109.1	83.8
42.5°	72.9	88.5	81.2	86.4	74.5
45°	57.9	71.9	71.9	71.9	58.5
47.5°	32.1	48.1	61.6	49.1	34.1
50°	18.1	24.3	47.6	25.3	19.1
52.5°	12.4	14.0	32.6	14.5	12.9
55°	9.3	9.8	17.6	10.3	9.8
57.5°	7.2	7.8	9.3	7.8	7.2
60°	5.7	5.7	6.7	6.2	5.7
62.5°	4.1	4.1	4.7	4.1	4.1
65°	3.1	3.1	3.1	3.1	3.1
67.5°	1.6	2.1	2.1	2.1	2.1
70°	1.6	1.0	1.0	1.0	1.6
72.5°	1.0	0.5	0.5	0.5	0.5
75°	0.0	0.0	0.5	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)