

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746779

Luminaire Tested: LD4D35BD010-EU4DR3020359030-4LBS1H

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P746779  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D35BD010-EU4DR3020359030-4LBS1H  
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3284.9 lumens  
Efficiency: N/A  
Efficacy: 106.7 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P746779

CATALOG NUMBER: LD4D35BD010-EU4DR3020359030-4LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P746779

CATALOG NUMBER: LD4D35BD010-EU4DR3020359030-4LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	808490	808490	808490
5°	785285	784363	785323
10°	680172	675377	680009
15°	443780	441395	439176
20°	220672	228948	220379
25°	111161	125350	108881
30°	44502	48497	38774
35°	20641	19772	16577
40°	8913	9892	8393
45°	6289	7805	6343
50°	2167	5680	2286
55°	1241	2349	1321
60°	873	1026	873
65°	561	561	561
70°	358	224	358
75°	0	148	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 7805 cd/sqm



TEST NUMBER: P746779

CATALOG NUMBER: LD4D35BD010-EU4DR3020359030-4LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	928.8	28.3
10°-20°	1495.9	45.5
20°-30°	646.4	19.7
30°-40°	147.3	4.5
40°-50°	50.6	1.5
50°-60°	12.4	0.4
60°-70°	3.2	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3071.1	93.5
0°-40°	3218.4	98.0
0°-60°	3281.3	99.9
0°-90°	3284.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3284.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	10562	10562	10562	10562	10562	
5°	10220	10210	10208	10230	10221	930
15°	5600	5533	5570	5552	5542	1500
25°	1316	1366	1484	1331	1289	630
35°	221	226	212	210	177	150
45°	58	72	72	72	59	41
55°	9	10	18	10	10	9
65°	3	3	3	3	3	3
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P746779

CATALOG NUMBER: LD4D35BD010-EU4DR3020359030-4LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	10562.5	10562.5	10562.5	10562.5	10562.5
2.5°	10492.5	10485.2	10489.4	10494.6	10496.7
5°	10220.3	10210.4	10208.3	10229.6	10220.8
7.5°	9671.1	9657.1	9635.8	9684.0	9729.2
10°	8751.1	8735.5	8689.4	8712.2	8749.0
12.5°	7392.9	7342.6	7341.6	7414.2	7404.3
15°	5600.2	5532.8	5570.1	5552.0	5542.1
17.5°	3766.0	3740.0	3789.8	3774.8	3709.9
20°	2709.1	2715.8	2810.7	2763.0	2705.5
22.5°	1976.8	2001.2	2113.7	1990.8	1945.7
25°	1316.2	1366.0	1484.2	1331.2	1289.2
27.5°	809.5	832.3	952.1	799.1	776.3
30°	503.5	492.1	548.7	470.9	438.7
32.5°	330.3	315.8	334.0	299.7	273.8
35°	220.9	225.6	211.6	210.0	177.4
37.5°	137.9	158.7	140.0	149.4	114.1
40°	89.2	115.1	99.0	109.4	84.0
42.5°	73.1	88.7	81.4	86.6	74.7
45°	58.1	72.1	72.1	72.1	58.6
47.5°	32.2	48.2	61.7	49.3	34.2
50°	18.2	24.4	47.7	25.4	19.2
52.5°	12.4	14.0	32.7	14.5	13.0
55°	9.3	9.9	17.6	10.4	9.9
57.5°	7.3	7.8	9.3	7.8	7.3
60°	5.7	5.7	6.7	6.2	5.7
62.5°	4.1	4.1	4.7	4.1	4.1
65°	3.1	3.1	3.1	3.1	3.1
67.5°	1.6	2.1	2.1	2.1	2.1
70°	1.6	1.0	1.0	1.0	1.6
72.5°	1.0	0.5	0.5	0.5	0.5
75°	0.0	0.0	0.5	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)