

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746792

Luminaire Tested: LD4D35BD010-EU4DR3020359035-4LBS1H

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P746792  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D35BD010-EU4DR3020359035-4LBS1H  
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3319.5 lumens  
Efficiency: N/A  
Efficacy: 107.8 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P746792

CATALOG NUMBER: LD4D35BD010-EU4DR3020359035-4LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P746792

CATALOG NUMBER: LD4D35BD010-EU4DR3020359035-4LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	817009	817009	817009
5°	793552	792630	793591
10°	687338	682488	687175
15°	448455	446046	443804
20°	222993	231359	222700
25°	112327	126668	110030
30°	44970	49000	39181
35°	20856	19978	16745
40°	9003	10002	8483
45°	6354	7881	6408
50°	2179	5740	2310
55°	1254	2375	1334
60°	888	1041	888
65°	561	561	561
70°	358	224	358
75°	0	148	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 7881 cd/sqm



TEST NUMBER: P746792

CATALOG NUMBER: LD4D35BD010-EU4DR3020359035-4LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	938.6	28.3
10°-20°	1511.6	45.5
20°-30°	653.2	19.7
30°-40°	148.9	4.5
40°-50°	51.1	1.5
50°-60°	12.5	0.4
60°-70°	3.2	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3103.4	93.5
0°-40°	3252.3	98.0
0°-60°	3315.9	99.9
0°-90°	3319.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3319.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	10674	10674	10674	10674	10674	
5°	10328	10318	10316	10337	10328	939
15°	5659	5591	5629	5610	5600	1515
25°	1330	1380	1500	1345	1303	637
35°	223	228	214	212	179	151
45°	59	73	73	73	59	42
55°	9	10	18	10	10	9
65°	3	3	3	3	3	3
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P746792

CATALOG NUMBER: LD4D35BD010-EU4DR3020359035-4LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	10673.8	10673.8	10673.8	10673.8	10673.8
2.5°	10603.0	10595.7	10599.9	10605.1	10607.2
5°	10327.9	10317.9	10315.9	10337.3	10328.4
7.5°	9772.9	9758.8	9737.3	9786.0	9831.6
10°	8843.3	8827.6	8780.9	8804.0	8841.2
12.5°	7470.8	7420.0	7418.9	7492.3	7482.3
15°	5659.2	5591.1	5628.8	5610.4	5600.5
17.5°	3805.6	3779.4	3829.7	3814.5	3749.0
20°	2737.6	2744.4	2840.3	2792.1	2734.0
22.5°	1997.7	2022.3	2136.0	2011.8	1966.2
25°	1330.0	1380.3	1499.8	1345.2	1302.8
27.5°	818.0	841.1	962.1	807.6	784.5
30°	508.8	497.3	554.4	475.8	443.3
32.5°	333.8	319.1	337.5	302.9	276.7
35°	223.2	228.0	213.8	212.2	179.2
37.5°	139.4	160.4	141.5	150.9	115.3
40°	90.1	116.3	100.1	110.6	84.9
42.5°	73.9	89.6	82.3	87.5	75.5
45°	58.7	72.8	72.8	72.8	59.2
47.5°	32.5	48.7	62.4	49.8	34.6
50°	18.3	24.6	48.2	25.7	19.4
52.5°	12.6	14.1	33.0	14.7	13.1
55°	9.4	10.0	17.8	10.5	10.0
57.5°	7.3	7.9	9.4	7.9	7.3
60°	5.8	5.8	6.8	6.3	5.8
62.5°	4.2	4.2	4.7	4.2	4.2
65°	3.1	3.1	3.1	3.1	3.1
67.5°	1.6	2.1	2.1	2.1	2.1
70°	1.6	1.0	1.0	1.0	1.6
72.5°	1.0	0.5	0.5	0.5	0.5
75°	0.0	0.0	0.5	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)