

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747285

Luminaire Tested: LD4D35BD010-EU4DR6020359050-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P747285
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR6020359050-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3367.6 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P747285
CATALOG NUMBER: LD4D35BD010-EU4DR6020359050-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P747285
 CATALOG NUMBER: LD4D35BD010-EU4DR6020359050-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87				
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81				
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75				
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70				
6	87	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65				
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61				
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57				
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53				
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	368209
5°	367312
10°	379514
15°	379908
20°	349551
25°	297315
30°	226552
35°	160206
40°	94079
45°	37965
50°	12680
55°	6096
60°	2513
65°	362
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 37965 cd/sqm



TEST NUMBER: P747285

CATALOG NUMBER: LD4D35BD010-EU4DR6020359050-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	323.1	9.6
10°-20°	930.4	27.6
20°-30°	1113.6	33.1
30°-40°	744.8	22.1
40°-50°	220.8	6.6
50°-60°	31.8	0.9
60°-70°	3.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2367.1	70.3
0°-40°	3112.0	92.4
0°-60°	3364.6	99.9
0°-90°	3367.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3367.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3370	
5°	3349	323
15°	3359	930
25°	2466	1114
35°	1201	745
45°	246	221
55°	32	32
65°	1	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P747285

CATALOG NUMBER: LD4D35BD010-EU4DR6020359050-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3370.0
2.5°	3365.7
5°	3349.0
7.5°	3394.4
10°	3420.7
12.5°	3415.9
15°	3358.6
17.5°	3223.3
20°	3006.3
22.5°	2745.8
25°	2466.2
27.5°	2151.3
30°	1795.7
32.5°	1478.3
35°	1201.1
37.5°	923.4
40°	659.6
42.5°	434.9
45°	245.7
47.5°	125.7
50°	74.6
52.5°	48.3
55°	32.0
57.5°	20.6
60°	11.5
62.5°	4.8
65°	1.4
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)