

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747528

Luminaire Tested: LD4D40BD010-EU4DR3040509024-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P747528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D40BD010-EU4DR3040509024-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2534.3 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P747528

CATALOG NUMBER: LD4D40BD010-EU4DR3040509024-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P747528

CATALOG NUMBER: LD4D40BD010-EU4DR3040509024-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	623767	623767	623767
5°	605858	605151	605889
10°	524770	521063	524646
15°	342388	340549	338830
20°	170251	176637	170023
25°	85757	96711	84000
30°	34337	37413	29918
35°	15923	15250	12783
40°	6875	7634	6475
45°	4850	6019	4893
50°	1667	4382	1762
55°	961	1815	1014
60°	674	796	674
65°	435	435	435
70°	269	179	269
75°	0	118	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 6019 cd/sqm



TEST NUMBER: P747528

CATALOG NUMBER: LD4D40BD010-EU4DR3040509024-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	716.6	28.3
10°-20°	1154.1	45.5
20°-30°	498.7	19.7
30°-40°	113.7	4.5
40°-50°	39.0	1.5
50°-60°	9.5	0.4
60°-70°	2.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2369.4	93.5
0°-40°	2483.1	98.0
0°-60°	2531.6	99.9
0°-90°	2534.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2534.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	8149	8149	8149	8149	8149	
5°	7885	7878	7876	7892	7886	717
15°	4321	4269	4298	4283	4276	1157
25°	1015	1054	1145	1027	995	486
35°	170	174	163	162	137	116
45°	45	56	56	56	45	32
55°	7	8	14	8	8	7
65°	2	2	2	2	2	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P747528

CATALOG NUMBER: LD4D40BD010-EU4DR3040509024-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	8149.2	8149.2	8149.2	8149.2	8149.2
2.5°	8095.2	8089.6	8092.8	8096.8	8098.4
5°	7885.1	7877.5	7875.9	7892.3	7885.5
7.5°	7461.4	7450.6	7434.2	7471.4	7506.2
10°	6751.7	6739.7	6704.0	6721.6	6750.1
12.5°	5703.8	5665.0	5664.2	5720.2	5712.6
15°	4320.7	4268.6	4297.5	4283.4	4275.8
17.5°	2905.5	2885.5	2923.9	2912.3	2862.3
20°	2090.1	2095.3	2168.5	2131.7	2087.3
22.5°	1525.2	1544.0	1630.8	1536.0	1501.2
25°	1015.4	1053.9	1145.1	1027.1	994.6
27.5°	624.6	642.2	734.6	616.6	598.9
30°	388.5	379.7	423.3	363.3	338.5
32.5°	254.9	243.7	257.7	231.3	211.3
35°	170.4	174.0	163.2	162.0	136.8
37.5°	106.4	122.4	108.0	115.2	88.0
40°	68.8	88.8	76.4	84.4	64.8
42.5°	56.4	68.4	62.8	66.8	57.6
45°	44.8	55.6	55.6	55.6	45.2
47.5°	24.8	37.2	47.6	38.0	26.4
50°	14.0	18.8	36.8	19.6	14.8
52.5°	9.6	10.8	25.2	11.2	10.0
55°	7.2	7.6	13.6	8.0	7.6
57.5°	5.6	6.0	7.2	6.0	5.6
60°	4.4	4.4	5.2	4.8	4.4
62.5°	3.2	3.2	3.6	3.2	3.2
65°	2.4	2.4	2.4	2.4	2.4
67.5°	1.2	1.6	1.6	1.6	1.6
70°	1.2	0.8	0.8	0.8	1.2
72.5°	0.8	0.4	0.4	0.4	0.4
75°	0.0	0.0	0.4	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)