

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747762

Luminaire Tested: LD4D40BD010-EU4DR4540509024-4LBDP1B

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P747762  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D40BD010-EU4DR4540509024-4LBDP1B  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 45° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2910.4 lumens  
Efficiency: N/A  
Efficacy: 82.7 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P747762  
CATALOG NUMBER: LD4D40BD010-EU4DR4540509024-4LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P747762

CATALOG NUMBER: LD4D40BD010-EU4DR4540509024-4LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95		
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90		
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85		
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81		
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77		
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73		
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69		
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66		
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63		
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	562048
5°	546054
10°	522424
15°	478126
20°	379317
25°	236820
30°	130529
35°	58608
40°	23077
45°	10878
50°	5150
55°	2705
60°	1333
65°	310
70°	128
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10878 cd/sqm



TEST NUMBER: P747762

CATALOG NUMBER: LD4D40BD010-EU4DR4540509024-4LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	467.8	16.1
10°-20°	1151.3	39.6
20°-30°	911.7	31.3
30°-40°	303.6	10.4
40°-50°	60.2	2.1
50°-60°	13.7	0.5
60°-70°	2.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2530.8	87.0
0°-40°	2834.4	97.4
0°-60°	2908.3	99.9
0°-90°	2910.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2910.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5144	
5°	4979	468
15°	4227	1151
25°	1964	912
35°	439	304
45°	70	60
55°	14	14
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P747762

CATALOG NUMBER: LD4D40BD010-EU4DR4540509024-4LBDP1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5144.1
2.5°	5110.6
5°	4978.7
7.5°	4869.8
10°	4708.8
12.5°	4494.4
15°	4226.9
17.5°	3824.7
20°	3262.3
22.5°	2592.3
25°	1964.4
27.5°	1438.4
30°	1034.6
32.5°	703.6
35°	439.4
37.5°	260.6
40°	161.8
42.5°	106.4
45°	70.4
47.5°	45.3
50°	30.3
52.5°	20.2
55°	14.2
57.5°	9.3
60°	6.1
62.5°	3.2
65°	1.2
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)