

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748078

Luminaire Tested: LD4D40BD010-EU4DR6540509024-4LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P748078  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D40BD010-EU4DR6540509024-4LBS1B  
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2760.6 lumens  
Efficiency: N/A  
Efficacy: 78.4 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P748078  
CATALOG NUMBER: LD4D40BD010-EU4DR6540509024-4LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P748078

CATALOG NUMBER: LD4D40BD010-EU4DR6540509024-4LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	146395
5°	146022
10°	145896
15°	141401
20°	128729
25°	112180
30°	93302
35°	73929
40°	53353
45°	33707
50°	17572
55°	9337
60°	4906
65°	2695
70°	1127
75°	1241
80°	874
85°	737

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 33707 cd/sqm



TEST NUMBER: P748078

CATALOG NUMBER: LD4D40BD010-EU4DR6540509024-4LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	237.0	8.6
10°-20°	649.1	23.5
20°-30°	793.4	28.7
30°-40°	643.8	23.3
40°-50°	320.8	11.6
50°-60°	89.5	3.2
60°-70°	20.3	0.7
70°-80°	5.3	0.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1679.6	60.8
0°-40°	2323.4	84.2
0°-60°	2733.6	99.0
0°-90°	2760.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2760.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2507	
5°	2491	237
15°	2339	649
25°	1741	793
35°	1037	644
45°	408	321
55°	92	89
65°	20	20
75°	6	5
85°	1	1
90°	0	



TEST NUMBER: P748078

CATALOG NUMBER: LD4D40BD010-EU4DR6540509024-4LBS1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2506.6
2.5°	2504.7
5°	2490.7
7.5°	2482.6
10°	2460.1
12.5°	2414.5
15°	2338.6
17.5°	2220.0
20°	2071.2
22.5°	1910.6
25°	1740.8
27.5°	1559.2
30°	1383.5
32.5°	1210.0
35°	1036.9
37.5°	864.1
40°	699.8
42.5°	545.9
45°	408.1
47.5°	284.4
50°	193.4
52.5°	133.3
55°	91.7
57.5°	61.9
60°	42.0
62.5°	29.1
65°	19.5
67.5°	9.9
70°	6.6
72.5°	6.3
75°	5.5
77.5°	3.7
80°	2.6
82.5°	1.8
85°	1.1
87.5°	0.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)