

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748023

Luminaire Tested: LD4D40BD010-EU4DR6040509030-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P748023
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D40BD010-EU4DR6040509030-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3772.5 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P748023
CATALOG NUMBER: LD4D40BD010-EU4DR6040509030-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P748023

CATALOG NUMBER: LD4D40BD010-EU4DR6040509030-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	489532
5°	501580
10°	507635
15°	483589
20°	426373
25°	344862
30°	233276
35°	116897
40°	18955
45°	18558
50°	18936
55°	19220
60°	19754
65°	20191
70°	20669
75°	20939
80°	20198
85°	16799

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 20939 cd/sqm



TEST NUMBER: P748023

CATALOG NUMBER: LD4D40BD010-EU4DR6040509030-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	437.1	11.6
10°-20°	1182.5	31.3
20°-30°	1272.3	33.7
30°-40°	553.1	14.7
40°-50°	92.9	2.5
50°-60°	90.3	2.4
60°-70°	77.2	2.0
70°-80°	51.7	1.4
80°-90°	15.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2891.9	76.7
0°-40°	3445.0	91.3
0°-60°	3628.2	96.2
0°-90°	3772.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3772.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4480	
5°	4573	437
15°	4275	1183
25°	2861	1272
35°	876	553
45°	120	93
55°	101	90
65°	78	77
75°	50	52
85°	13	15
90°	0	



TEST NUMBER: P748023

CATALOG NUMBER: LD4D40BD010-EU4DR6040509030-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4480.4
2.5°	4606.4
5°	4573.2
7.5°	4583.6
10°	4575.5
12.5°	4481.0
15°	4275.2
17.5°	3998.8
20°	3667.0
22.5°	3311.9
25°	2860.6
27.5°	2288.0
30°	1849.0
32.5°	1425.1
35°	876.4
37.5°	374.9
40°	132.9
42.5°	122.4
45°	120.1
47.5°	116.0
50°	111.4
52.5°	106.1
55°	100.9
57.5°	95.6
60°	90.4
62.5°	84.5
65°	78.1
67.5°	71.7
70°	64.7
72.5°	57.1
75°	49.6
77.5°	40.8
80°	32.1
82.5°	22.7
85°	13.4
87.5°	4.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)