

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748102

Luminaire Tested: LD4D40BD010-EU4DR6540509030-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P748102
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D40BD010-EU4DR6540509030-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3461.2 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P748102
CATALOG NUMBER: LD4D40BD010-EU4DR6540509030-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P748102

CATALOG NUMBER: LD4D40BD010-EU4DR6540509030-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	372339
5°	372642
10°	385771
15°	386401
20°	355748
25°	303114
30°	232052
35°	163941
40°	96774
45°	39278
50°	14244
55°	7924
60°	4545
65°	2508
70°	2620
75°	2026
80°	2139
85°	1880

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 39278 cd/sqm



TEST NUMBER: P748102

CATALOG NUMBER: LD4D40BD010-EU4DR6540509030-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.1	9.5
10°-20°	946.5	27.3
20°-30°	1135.7	32.8
30°-40°	763.2	22.1
40°-50°	228.5	6.6
50°-60°	40.3	1.2
60°-70°	11.5	0.3
70°-80°	5.6	0.2
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2410.4	69.6
0°-40°	3173.6	91.7
0°-60°	3442.3	99.5
0°-90°	3461.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3461.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3408	
5°	3398	328
15°	3416	947
25°	2514	1136
35°	1229	763
45°	254	228
55°	42	40
65°	10	11
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P748102

CATALOG NUMBER: LD4D40BD010-EU4DR6540509030-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3407.8
2.5°	3422.3
5°	3397.6
7.5°	3449.0
10°	3477.1
12.5°	3470.3
15°	3416.0
17.5°	3283.3
20°	3059.6
22.5°	2796.2
25°	2514.3
27.5°	2196.2
30°	1839.3
32.5°	1515.8
35°	1229.1
37.5°	945.8
40°	678.5
42.5°	443.1
45°	254.2
47.5°	134.6
50°	83.8
52.5°	58.1
55°	41.6
57.5°	30.0
60°	20.8
62.5°	13.6
65°	9.7
67.5°	8.7
70°	8.2
72.5°	6.3
75°	4.8
77.5°	4.4
80°	3.4
82.5°	2.4
85°	1.5
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)