

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748908

Luminaire Tested: LD4D45BD010-EU4DR6540509040-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P748908
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR6540509040-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4010.4 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P748908

CATALOG NUMBER: LD4D45BD010-EU4DR6540509040-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P748908

CATALOG NUMBER: LD4D45BD010-EU4DR6540509040-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69		
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65		
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57		
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	431416
5°	431781
10°	446980
15°	447721
20°	412199
25°	351216
30°	268867
35°	189950
40°	112121
45°	45521
50°	16505
55°	9201
60°	5266
65°	2896
70°	3035
75°	2364
80°	2454
85°	2131

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 45521 cd/sqm



TEST NUMBER: P748908

CATALOG NUMBER: LD4D45BD010-EU4DR6540509040-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	380.2	9.5
10°-20°	1096.7	27.3
20°-30°	1315.9	32.8
30°-40°	884.3	22.1
40°-50°	264.7	6.6
50°-60°	46.7	1.2
60°-70°	13.3	0.3
70°-80°	6.5	0.2
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2792.8	69.6
0°-40°	3677.1	91.7
0°-60°	3988.6	99.5
0°-90°	4010.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4010.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3948	
5°	3937	380
15°	3958	1097
25°	2913	1316
35°	1424	884
45°	295	265
55°	48	47
65°	11	13
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P748908

CATALOG NUMBER: LD4D45BD010-EU4DR6540509040-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3948.5
2.5°	3965.4
5°	3936.8
7.5°	3996.2
10°	4028.8
12.5°	4020.9
15°	3958.1
17.5°	3804.3
20°	3545.1
22.5°	3239.9
25°	2913.3
27.5°	2544.6
30°	2131.1
32.5°	1756.3
35°	1424.1
37.5°	1095.9
40°	786.1
42.5°	513.4
45°	294.6
47.5°	156.0
50°	97.1
52.5°	67.3
55°	48.3
57.5°	34.8
60°	24.1
62.5°	15.7
65°	11.2
67.5°	10.1
70°	9.5
72.5°	7.3
75°	5.6
77.5°	5.1
80°	3.9
82.5°	2.8
85°	1.7
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)