

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748457

Luminaire Tested: LD4D45BD010-EU4DR3540509050-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P748457
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR3540509050-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4634.6 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P748457
CATALOG NUMBER: LD4D45BD010-EU4DR3540509050-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P748457

CATALOG NUMBER: LD4D45BD010-EU4DR3540509050-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96			96
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92			92
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88			88
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84			84
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81			81
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78			78
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75			75
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72			72
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70			70
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68			68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1393282
5°	1360546
10°	1226212
15°	951739
20°	539808
25°	210008
30°	78348
35°	42949
40°	28070
45°	17090
50°	10879
55°	7677
60°	5616
65°	3051
70°	224
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17090 cd/sqm



TEST NUMBER: P748457

CATALOG NUMBER: LD4D45BD010-EU4DR3540509050-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1140.9	24.6
10°-20°	2227.5	48.1
20°-30°	908.5	19.6
30°-40°	217.4	4.7
40°-50°	90.6	2.0
50°-60°	37.5	0.8
60°-70°	11.7	0.3
70°-80°	0.3	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4276.8	92.3
0°-40°	4494.2	97.0
0°-60°	4622.4	99.7
0°-90°	4634.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4634.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12752	
5°	12405	###
15°	8414	2227
25°	1742	908
35°	322	217
45°	111	91
55°	40	38
65°	12	12
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P748457

CATALOG NUMBER: LD4D45BD010-EU4DR3540509050-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	12751.9
2.5°	12675.4
5°	12404.9
7.5°	11865.2
10°	11052.3
12.5°	9907.6
15°	8413.9
17.5°	6587.0
20°	4642.6
22.5°	2960.4
25°	1742.0
27.5°	984.7
30°	621.0
32.5°	436.0
35°	322.0
37.5°	249.0
40°	196.8
42.5°	151.6
45°	110.6
47.5°	82.8
50°	64.0
52.5°	50.8
55°	40.3
57.5°	32.7
60°	25.7
62.5°	18.8
65°	11.8
67.5°	4.2
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)