

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748924

Luminaire Tested: LD4D45BD010-EU4DR6540509050-4LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P748924  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D45BD010-EU4DR6540509050-4LBS1H  
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4049.2 lumens  
Efficiency: N/A  
Efficacy: 104.6 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 38.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P748924

CATALOG NUMBER: LD4D45BD010-EU4DR6540509050-4LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P748924

CATALOG NUMBER: LD4D45BD010-EU4DR6540509050-4LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	214728
5°	214182
10°	214002
15°	207404
20°	188818
25°	164539
30°	136854
35°	108437
40°	78261
45°	49442
50°	25768
55°	13695
60°	7195
65°	3952
70°	1656
75°	1828
80°	1278
85°	1072

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 49442 cd/sqm



TEST NUMBER: P748924

CATALOG NUMBER: LD4D45BD010-EU4DR6540509050-4LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	347.7	8.6
10°-20°	952.1	23.5
20°-30°	1163.8	28.7
30°-40°	944.3	23.3
40°-50°	470.5	11.6
50°-60°	131.2	3.2
60°-70°	29.8	0.7
70°-80°	7.8	0.2
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2463.6	60.8
0°-40°	3407.8	84.2
0°-60°	4009.6	99.0
0°-90°	4049.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4049.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3677	
5°	3653	348
15°	3430	952
25°	2553	1164
35°	1521	944
45°	599	471
55°	134	131
65°	29	30
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P748924

CATALOG NUMBER: LD4D45BD010-EU4DR6540509050-4LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3676.6
2.5°	3673.9
5°	3653.3
7.5°	3641.4
10°	3608.5
12.5°	3541.5
15°	3430.2
17.5°	3256.2
20°	3038.0
22.5°	2802.4
25°	2553.3
27.5°	2287.0
30°	2029.3
32.5°	1774.8
35°	1520.9
37.5°	1267.5
40°	1026.5
42.5°	800.7
45°	598.6
47.5°	417.1
50°	283.6
52.5°	195.6
55°	134.5
57.5°	90.8
60°	61.6
62.5°	42.7
65°	28.6
67.5°	14.6
70°	9.7
72.5°	9.2
75°	8.1
77.5°	5.4
80°	3.8
82.5°	2.7
85°	1.6
87.5°	1.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)