

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740129

Luminaire Tested: LD4D05D010-EU4DR300210IC9040-4LBS1H

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P740129  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D05D010-EU4DR300210IC9040-4LBS1H  
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 708.6 lumens  
Efficiency: N/A  
Efficacy: 94.5 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P740129  
CATALOG NUMBER: LD4D05D010-EU4DR300210IC9040-4LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P740129

CATALOG NUMBER: LD4D05D010-EU4DR300210IC9040-4LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	174396	174396	174396
5°	169392	169192	169400
10°	146720	145686	146681
15°	95726	95211	94736
20°	47603	49387	47538
25°	23977	27043	23487
30°	9599	10465	8370
35°	4457	4270	3579
40°	1928	2138	1809
45°	1353	1678	1375
50°	464	1227	488
55°	267	507	280
60°	184	214	184
65°	127	127	127
70°	67	45	67
75°	0	30	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 1678 cd/sqm



TEST NUMBER: P740129

CATALOG NUMBER: LD4D05D010-EU4DR300210IC9040-4LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	200.4	28.3
10°-20°	322.7	45.5
20°-30°	139.4	19.7
30°-40°	31.8	4.5
40°-50°	10.9	1.5
50°-60°	2.7	0.4
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	662.5	93.5
0°-40°	694.2	98.0
0°-60°	707.8	99.9
0°-90°	708.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	708.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2278	2278	2278	2278	2278	
5°	2205	2202	2202	2207	2205	201
15°	1208	1194	1202	1198	1196	323
25°	284	295	320	287	278	136
35°	48	49	46	45	38	32
45°	12	16	16	16	13	9
55°	2	2	4	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P740129

CATALOG NUMBER: LD4D05D010-EU4DR300210IC9040-4LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2278.4	2278.4	2278.4	2278.4	2278.4
2.5°	2263.3	2261.8	2262.6	2263.8	2264.2
5°	2204.6	2202.5	2202.0	2206.6	2204.7
7.5°	2086.1	2083.1	2078.5	2088.9	2098.7
10°	1887.7	1884.3	1874.4	1879.3	1887.2
12.5°	1594.7	1583.9	1583.6	1599.3	1597.2
15°	1208.0	1193.5	1201.5	1197.6	1195.5
17.5°	812.3	806.8	817.5	814.2	800.2
20°	584.4	585.8	606.3	596.0	583.6
22.5°	426.4	431.7	456.0	429.4	419.7
25°	283.9	294.7	320.2	287.2	278.1
27.5°	174.6	179.6	205.4	172.4	167.5
30°	108.6	106.2	118.4	101.6	94.7
32.5°	71.3	68.1	72.0	64.6	59.1
35°	47.7	48.6	45.7	45.3	38.3
37.5°	29.7	34.2	30.2	32.2	24.6
40°	19.3	24.8	21.4	23.6	18.1
42.5°	15.8	19.1	17.6	18.7	16.1
45°	12.5	15.5	15.5	15.5	12.7
47.5°	6.9	10.4	13.3	10.6	7.4
50°	3.9	5.3	10.3	5.5	4.1
52.5°	2.7	3.0	7.0	3.2	2.8
55°	2.0	2.1	3.8	2.2	2.1
57.5°	1.5	1.7	2.0	1.7	1.5
60°	1.2	1.2	1.4	1.3	1.2
62.5°	0.9	0.9	1.0	0.9	0.9
65°	0.7	0.7	0.7	0.7	0.7
67.5°	0.3	0.5	0.5	0.5	0.5
70°	0.3	0.2	0.2	0.2	0.3
72.5°	0.2	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)