

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740143

Luminaire Tested: LD4D05D010-EU4DR300210IC9050-4LBS1LI

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P740143  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D05D010-EU4DR300210IC9050-4LBS1LI  
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 735.2 lumens  
Efficiency: N/A  
Efficacy: 98.0 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P740143  
CATALOG NUMBER: LD4D05D010-EU4DR300210IC9050-4LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P740143

CATALOG NUMBER: LD4D05D010-EU4DR300210IC9050-4LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	180956	180956	180956
5°	175762	175562	175770
10°	152238	151166	152200
15°	99324	98793	98294
20°	49395	51244	49330
25°	24881	28056	24366
30°	9961	10854	8679
35°	4616	4429	3710
40°	1988	2218	1879
45°	1407	1754	1418
50°	488	1274	512
55°	280	534	294
60°	199	230	199
65°	127	127	127
70°	67	45	67
75°	0	30	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 1754 cd/sqm



TEST NUMBER: P740143  
 CATALOG NUMBER: LD4D05D010-EU4DR300210IC9050-4LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	207.9	28.3
10°-20°	334.8	45.5
20°-30°	144.7	19.7
30°-40°	33.0	4.5
40°-50°	11.3	1.5
50°-60°	2.8	0.4
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	687.4	93.5
0°-40°	720.4	98.0
0°-60°	734.5	99.9
0°-90°	735.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	735.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2364	2364	2364	2364	2364	
5°	2288	2285	2285	2290	2288	208
15°	1253	1238	1247	1243	1240	336
25°	295	306	332	298	288	141
35°	49	50	47	47	40	34
45°	13	16	16	16	13	9
55°	2	2	4	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P740143

CATALOG NUMBER: LD4D05D010-EU4DR300210IC9050-4LBS1LI

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2364.1	2364.1	2364.1	2364.1	2364.1
2.5°	2348.5	2346.9	2347.8	2348.9	2349.4
5°	2287.5	2285.3	2284.9	2289.6	2287.6
7.5°	2164.6	2161.5	2156.7	2167.5	2177.6
10°	1958.7	1955.2	1944.9	1950.0	1958.2
12.5°	1654.7	1643.5	1643.2	1659.4	1657.3
15°	1253.4	1238.4	1246.7	1242.7	1240.4
17.5°	842.9	837.1	848.3	844.9	830.4
20°	606.4	607.8	629.1	618.4	605.6
22.5°	442.5	447.9	473.1	445.6	435.5
25°	294.6	305.7	332.2	297.9	288.5
27.5°	181.2	186.3	213.1	178.9	173.8
30°	112.7	110.2	122.8	105.4	98.2
32.5°	73.9	70.7	74.8	67.1	61.3
35°	49.4	50.5	47.4	47.0	39.7
37.5°	30.9	35.5	31.3	33.4	25.6
40°	19.9	25.8	22.2	24.5	18.8
42.5°	16.4	19.8	18.2	19.4	16.7
45°	13.0	16.2	16.2	16.2	13.1
47.5°	7.2	10.8	13.8	11.0	7.7
50°	4.1	5.4	10.7	5.7	4.3
52.5°	2.8	3.2	7.3	3.3	2.9
55°	2.1	2.2	4.0	2.3	2.2
57.5°	1.6	1.7	2.1	1.7	1.6
60°	1.3	1.3	1.5	1.4	1.3
62.5°	0.9	0.9	1.0	0.9	0.9
65°	0.7	0.7	0.7	0.7	0.7
67.5°	0.3	0.5	0.5	0.5	0.5
70°	0.3	0.2	0.2	0.2	0.3
72.5°	0.2	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)