

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749665

Luminaire Tested: LD4D50D010-EU4DR6540509030-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P749665
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D50D010-EU4DR6540509030-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4463.8 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P749665
CATALOG NUMBER: LD4D50D010-EU4DR6540509030-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P749665

CATALOG NUMBER: LD4D50D010-EU4DR6540509030-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	236711
5°	236114
10°	235909
15°	228639
20°	208147
25°	181390
30°	150861
35°	119538
40°	86274
45°	54505
50°	28412
55°	15101
60°	7931
65°	4367
70°	1827
75°	2008
80°	1413
85°	1206

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 54505 cd/sqm



TEST NUMBER: P749665

CATALOG NUMBER: LD4D50D010-EU4DR6540509030-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	383.3	8.6
10°-20°	1049.6	23.5
20°-30°	1282.9	28.7
30°-40°	1040.9	23.3
40°-50°	518.7	11.6
50°-60°	144.7	3.2
60°-70°	32.9	0.7
70°-80°	8.6	0.2
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2715.8	60.8
0°-40°	3756.7	84.2
0°-60°	4420.2	99.0
0°-90°	4463.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4463.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4053	
5°	4027	383
15°	3781	1050
25°	2815	1283
35°	1677	1041
45°	660	519
55°	148	145
65°	32	33
75°	9	9
85°	2	2
90°	0	



TEST NUMBER: P749665
CATALOG NUMBER: LD4D50D010-EU4DR6540509030-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4053.0
2.5°	4050.0
5°	4027.4
7.5°	4014.3
10°	3977.9
12.5°	3904.1
15°	3781.4
17.5°	3589.6
20°	3349.0
22.5°	3089.3
25°	2814.8
27.5°	2521.1
30°	2237.0
32.5°	1956.5
35°	1676.6
37.5°	1397.3
40°	1131.6
42.5°	882.7
45°	659.9
47.5°	459.8
50°	312.7
52.5°	215.6
55°	148.3
57.5°	100.1
60°	67.9
62.5°	47.1
65°	31.6
67.5°	16.1
70°	10.7
72.5°	10.1
75°	8.9
77.5°	6.0
80°	4.2
82.5°	3.0
85°	1.8
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)